

# AR4018SPX429

APC NetShelter CX, 18U, Soundproof Server Rack Enclosure, 100V to 240V, Black, 1015H x 750W x 1130D mm



## Overview

|              |                                                                                                                                                                                                                                                                                                                                                                                                                 |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | NetShelter CX Enclosure with integrated cooling and noise dampening is ideal for office environments. The cabinet is paired with a shock absorbing pallet, unloading ramp and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS). |
| Lead time    | Usually Ships within 8 Weeks                                                                                                                                                                                                                                                                                                                                                                                    |

## Main

|                     |                                                                                        |
|---------------------|----------------------------------------------------------------------------------------|
| Main Input Voltage  | 100 V<br>110 V<br>115 V<br>120 V<br>127 V<br>200 V<br>208 V<br>220 V<br>230 V<br>240 V |
| Plug standard       | IEC 60320 C14                                                                          |
| Number of rack unit | 18U                                                                                    |
| Provided equipment  | Key(S)<br>Leveling feet<br>Pallet ramps<br>Reusable packaging<br>Unpacking sheet       |

## Physical

|                            |                                                                  |
|----------------------------|------------------------------------------------------------------|
| Color                      | Black                                                            |
| Height                     | 39.96 in (101.5 cm)                                              |
| Width                      | 29.53 in (75 cm)                                                 |
| Depth                      | 44.49 in (113 cm)                                                |
| Net Weight                 | 317.47 lb(US) (144 kg)                                           |
| Mounting preference        | No preference                                                    |
| Mounting Mode              | Not rack-mountable                                               |
| Maximum Mounting Depth     | 33.94 in (86.21 cm)                                              |
| Rack Width                 | 19"                                                              |
| Permanent permissible load | 700 Lb(US) (317.51 kg) dynamic<br>1826 lb(US) (828.26 kg) static |

## Input

|                 |                                |
|-----------------|--------------------------------|
| Input Frequency | 50/60 Hz +/- 3 Hz auto-sensing |
|-----------------|--------------------------------|

## Conformance

|           |          |
|-----------|----------|
| Standards | EIA-310D |
|-----------|----------|

## Ordering and shipping details

|                     |                        |
|---------------------|------------------------|
| GTIN                | 731304338567           |
| Package weight(Lbs) | 485.02 lb(US) (220 kg) |

## Packing Units

|                              |                   |
|------------------------------|-------------------|
| Package 1 Height             | 50.39 in (128 cm) |
| Package 1 width              | 39.37 in (100 cm) |
| Package 1 Length             | 51.18 in (130 cm) |
| Number of Units in Package 3 | 1                 |

## Offer Sustainability

|                             |                                                                                                                                                                                    |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status    | Green Premium product                                                                                                                                                              |
| REACH Regulation            |  <a href="#">REACH Declaration</a>                                                                |
| REACH free of SVHC          | Yes                                                                                                                                                                                |
| EU RoHS Directive           | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Optimized Energy Efficiency | Energy efficient product                                                                                                                                                           |
| Take-back                   | Take-back program available                                                                                                                                                        |

## Contractual warranty

|          |                                |
|----------|--------------------------------|
| Warranty | 2 year (manufacturer's defect) |
|----------|--------------------------------|