



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Provided Equipment	Installation guide
--------------------	--------------------

Physical

Color	Beige
Height	0.98 in (2.5 cm)
Width	47.99 in (121.9 cm)
Depth	15.98 in (40.6 cm)
Net Weight	1.81 lb(US) (0.82 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	-35...165 °F (-37...74 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...3000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)



Ordering and shipping details

GTIN	731304329923
Package weight(Lbs)	2.60 lb(US) (1.18 kg)

Packing Units

Package 1 Height	2.01 in (5.1 cm)
Package 1 width	17.48 in (44.4 cm)
Package 1 Length	17.48 in (44.4 cm)

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------