

Product data sheet

Characteristics

AP8865X630

Rack PDU 2G, Metered, ZeroU, 8.6kW, 208V,
(36) C13 & (6) C19 & (2) 5-20, 10ft. Cord



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Installation guide Rack Mounting brackets
--------------------	--

Physical

Color	Black
Depth	1.81 in (4.6 cm)
Height	70.51 in (179.1 cm)
Product Weight	18.74 lb(US) (8.5 kg)
Width	2.20 in (5.6 cm)

Conformance

Standards	CSA C22.2 No. 60950 UL 60950-1
-----------	-----------------------------------

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304290865
Package weight(Lbs)	22.35 lb(US) (10.14 kg)

Packing Units

Package 1 Height	78.74 in (200 cm)
Package 1 width	6.38 in (16.2 cm)
Package 1 Length	4.21 in (10.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------