

AR4000MVA

APC NetShelter CX, Mini, Soundproof Server
Rack Enclosure, 12U, 100V to 240V, Oak,
744H x 688W x 952D mm



Overview

Presentation	Netshelter CX Mini is specifically designed to house a complete small-office IT installation comprised of one or two servers, network hardware and peripheral devices. It combines extreme noise reduction and moderate thermal capacity with exceptional reliability and an all-inclusive, plug-and-play specification. The CX Mini now comes with 12U rack mount conversion kit pre-installed, resulting in an EIA rack that is 600mm/23.6" deep. NAM power cords sold separately, part number AR4605.
Lead time	Usually in Stock

Main

Main Input Voltage	100 V 120 V 200 V 208 V 230 V 240 V
Plug standard	IEC 60320 C14
Number of rack unit	12U
Provided equipment	Brush strips Door Key(S) Lockable door Office-type Casters Power strip with (3) IEC receptacles 2 x Fans Soundproofing Unpacking sheet

Physical

Color	Oak
Height	27.56 in (70 cm)
Width	27.17 in (69 cm)
Depth	36.61 in (93 cm)
Net Weight	165.35 lb(US) (75 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	27.17 in (69.01 cm)
Rack Width	19"
Permanent permissible load	700 lb(US) (317.51 kg) static

Input

Input Frequency	50/60 Hz
-----------------	----------

Conformance

Product Certifications	TAA compliance
------------------------	----------------

Ordering and shipping details

GTIN	731304402732
Package weight(Lbs)	176.37 lb(US) (80 kg)

Packing Units

Package 1 Height	29.53 in (75 cm)
Package 1 width	29.13 in (74 cm)
Package 1 Length	38.58 in (98 cm)
Number of Units in Package 3	1

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------