

AR4038A

APC NetShelter CX, 38U, Soundproof Server Rack Enclosure, 100V to 120V, Grey and Oak, 1950H x 750W x 1130D mm



Overview

Presentation	Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.
Lead time	Usually in Stock

Main

Product or Component Type	Rack enclosure
Main Input Voltage	100 V 120 V
Main Output Voltage	100 V 120 V
Input Connection Type	NEMA 5-15P
Output connection type	11 NEMA 5-15R
Number of rack unit	38U
Provided equipment	Casters Key(S) Leveling feet Rack Power Distribution Unit (PDU) Side Panels Unpacking sheet

Physical

Height	76.77 in (195 cm)
Width	29.53 in (75 cm)
Depth	44.49 in (113 cm)
Net Weight	446.44 lb(US) (202.5 kg)
Color	Gray Oak
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	34.65 in (88.01 cm)
Minimum Mounting Depth	28.35 in (72.01 cm)
Rack width	19"
Permanent permissible load	1716 lb(US) (778.36 kg) static

Input

Input Frequency	50/60 Hz
-----------------	----------

Conformance

Product Certifications	TAA compliance
Standards	EIA-310D



Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304300281
Returnability	No
Country of origin	TH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	84.65 in (215 cm)
Package 1 Width	47.24 in (120 cm)
Package 1 Length	31.50 in (80 cm)
Package 1 Weight	507.06 lb(US) (230 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Take-back	Take-back program available

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------