



Main

Range	TeSys
Product name	TeSys CASK
Product or Component Type	Control relay
Device short name	CA2SK
Contactor application	Control circuit
Utilisation category	AC-15 DC-13
Pole contact composition	1 NO + 1 NC
[Ue] rated operational voltage	<= 690 V <= 400 Hz
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	277 V AC 50/60 Hz

Complementary

[Ith] conventional free air thermal current	10 A 131 °F (55 °C)
Associated fuse rating	10 A gL VDE 0660 10 A gL IEC 60947
[Ui] rated insulation voltage	690 V IEC 60947 690 V VDE 0110 group C 690 V BS 5424 690 V UL 508 690 V CSA C22.2 No 14
Mounting Support	Rail Plate
Connections - terminals	Screw clamp terminals 1 0.00...0.01 in ² (1.5...6 mm ²)solid Screw clamp terminals 2 0.00...0.01 in ² (1.5...4 mm ²)solid Screw clamp terminals 1 0.00...0.01 in ² (0.5...6 mm ²)flexible without cable end Screw clamp terminals 1 0.00...0.01 in ² (0.35...6 mm ²)flexible with cable end Screw clamp terminals 2 0.00...0.00 in ² (0.35...1.5 mm ²)flexible with cable end Screw clamp terminals 2 0.00...0.00 in ² (0.35...2.5 mm ²)flexible without cable end
Tightening torque	7.08 lbf.in (0.8 N.m) screw clamp terminals pozidriv No 1
Control circuit voltage limits	Drop-out 0.2...0.75 Uc 122 °F (50 °C)) Operational 0.85...1.1 Uc 122 °F (50 °C))
Operating time	6...8 ms coil de-energisation and NO opening 7...14 ms coil energisation and NO closing 8...10 ms coil de-energisation and NC closing 8...16 ms coil energisation and NC opening
Mechanical durability	10 Mcycles
Maximum operating rate	1200 cyc/h
Inrush power in VA	16 VA 68 °F (20 °C))
Hold-in power consumption in VA	4.2 VA 68 °F (20 °C))
Heat dissipation	1.4 W
Height	2.20 in (56 mm)
Width	1.06 in (27 mm)
Depth	2.19 in (55.5 mm)
Net Weight	0.29 lb(US) (0.132 kg)

Environment

Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1
Product Certifications	CB Scheme CULus EAC CE UKCA
IP degree of protection	IP2X
Protective treatment	TC IEC 60068
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Ambient Air Temperature for Storage	-58...158 °F (-50...70 °C)
Operating altitude	6561.68 ft (2000 m) without derating

Ordering and shipping details

Category	22371-RELAYS, CONTROL
Discount Schedule	I12
GTIN	3389110701609
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 in (3.3 cm)
Package 1 Width	2.64 in (6.7 cm)
Package 1 Length	2.32 in (5.9 cm)
Package 1 Weight	4.30 oz (122.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------