

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	L
-------------------	---

Complementary

Cable length	12 ft
Electrical connection	AWG 16 yellow STO cable
Product destination	Type P/AP connector
Connector type	4 pins female

Environment

Ambient air temperature for operation	<= 140 °F
---------------------------------------	-----------

Ordering and shipping details

Category	22426 - LIMIT SWITCHES,TYPE L
Discount Schedule	DS1
GTIN	00785901342045
Nbr. of units in pkg.	1
Package weight(Lbs)	1.5
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------