



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of cables	1
Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide

Physical

Color	Black
Height	3.70 in (9.4 cm)
Width	5.12 in (13 cm)
Depth	5.91 in (15 cm)
Net Weight	10.91 lb(US) (4.95 kg)
Mounting Mode	Not rack-mountable

Output

Battery Capacity	7.0 Ah
------------------	--------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery Voltage	24 V
RBC Quantity	1

Ordering and shipping details

GTIN	731304003311
Package weight(Lbs)	12.02 lb(US) (5.45 kg)

Packing Units

Package 1 Height	6.61 in (16.8 cm)
Package 1 width	6.61 in (16.8 cm)
Package 1 Length	8.82 in (22.4 cm)
Number of Units in Package 3	100

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------