



Overview

Presentation	Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack is packaged unassembled for smaller storage and delivery and takes up 60% less space than the assembled. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray can be top or bottom mounted (sold separately). Top and bottom feature knockouts of 1U or 2U mounting space for accessories. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 9U Wall mount cabinet, 8.9 to 12.9 inches mounting depth, 200lb weight capacity, 19" rack width, ships unassembled, 5 year APC warranty.
Lead time	Usually in Stock

Main

Product or Component Type	Rack enclosure
Number of rack unit	9U

Physical

Height	19.09 in (48.5 cm)
Width	23.58 in (59.9 cm)
Depth	15.75 in (40 cm)
Net Weight	28.00 lb(US) (12.7 kg)
Color	Black
Mounting Support	Wall
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	12.95 in (32.89 cm)
Minimum Mounting Depth	8.90 in (22.61 cm)
Rack width	19"
Permanent permissible load	200 lb(US) (90.72 kg) static

Conformance

Standards	EIA-310E
-----------	----------

Ordering and shipping details

GTIN	731304317272
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.54 in (29.3 cm)
Package 1 Width	19.09 in (48.5 cm)
Package 1 Length	27.09 in (68.8 cm)
Package 1 Weight	35.30 lb(US) (16.01 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------