



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	115 V
Plug standard	IEC 60320 C14
Number of cables	1

Physical

Color	Black
Height	1.69 in (4.3 cm)
Width	19.02 in (48.3 cm)
Depth	5.20 in (13.2 cm)
Net Weight	5.95 lb(US) (2.7 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
-----------------	-------

Conformance

Standards	UL 507
-----------	--------

Ordering and shipping details

GTIN	731304312130
Package weight(Lbs)	6.59 lb(US) (2.99 kg)

Packing Units

Package 1 Height	4.65 in (11.8 cm)
Package 1 width	22.80 in (57.9 cm)
Package 1 Length	8.11 in (20.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------