



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of rack unit	0U
Cable length	6 ft (1.83 m)
Product Compatibility	KVM Switch

Physical

Color	Black
Height	0.24 in (0.6 cm)
Width	0.24 in (0.6 cm)
Depth	0.24 in (0.6 cm)
Net Weight	0.24 lb(US) (0.11 kg)
Mounting Support	Hidden
Mounting Mode	Rack-mounted
Connector B	SUB-D 15HD female VGA Monitor
Connector A	USB 2.0 type A male

Output

Number of port	0
----------------	---

Ordering and shipping details

GTIN	731304221302
Package weight(Lbs)	0.99 lb(US) (0.45 kg)

Packing Units

Package 1 Height	2.01 in (5.1 cm)
Package 1 width	0.51 in (1.3 cm)
Package 1 Length	6.50 in (16.5 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------