



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	230 V
Input Connection Type	IEC 60320 C14
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets Toolless Mounting Kit

Physical

Color	Black
Height	49.02 in (124.5 cm)
Width	2.20 in (5.6 cm)
Depth	1.73 in (4.4 cm)
Net Weight	6.77 lb(US) (3.07 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Acceptable Input Voltage	200...250 V
Max line current	10 A
Load Capacity	2300 VA
Input Frequency	47...63 Hz

Output

Number of power socket outlets	16 IEC 60320 C13
--------------------------------	------------------

Conformance

Product Certifications	CE GOST VDE
------------------------	-------------------

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304331537
Package weight(Lbs)	8.77 lb(US) (3.98 kg)

Packing Units

Package 1 Height	84.02 in (213.4 cm)
Package 1 width	15.24 in (38.7 cm)
Package 1 Length	12.72 in (32.3 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------