



Overview

Presentation	StruxureWare Data Center Expert Standard scales up to 2025 devices and 125 surveillance cameras.
Lead time	Usually Ships within 2 Weeks

Main

Number of rack unit	1U
Number of cables	2
Communication port protocol	DNS HTTP HTTPS SMTP SMS SSL TCP/IP
Provided Equipment	1 Node Surveillance License Key 25-Node license key CD with software Server appliance User Manual Installation guide

General

Operating System	Windows 7 Windows 8 Windows Vista Windows XP Windows XP Professional SP1 Windows XP Professional SP2
Memory capacity	2GB/250GB available for data storage

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	19.02 in (48.3 cm)
Depth	19.02 in (48.3 cm)
Net Weight	21.05 lb(US) (9.55 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted

Conformance

Product Certifications	TAA compliance
------------------------	----------------

Environmental

Ambient Air Temperature for Operation	50...95 °F (10...35 °C)
Operating altitude	0...10000 ft
Relative Humidity	5...90 %
Ambient Air Temperature for Storage	-31...140 °F (-35...60 °C)
Storage altitude	0...30000 ft (0.00...9144.00 m)
Storage Relative Humidity	5...95 %

Communications & Management

Communication Network Type	RJ-45 10/100/1000 Base-T
----------------------------	--------------------------

Ordering and shipping details

GTIN	731304246022
Package weight(Lbs)	42.09 lb(US) (19.09 kg)

Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	24.76 in (62.9 cm)
Package 1 Length	35.00 in (88.9 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------