

APCRBC143US

APC Replacement Battery Cartridge #143 TAA with 2 Year Warranty



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Installation guide Reusable packaging

Physical

Height	8.86 in (22.5 cm)
Width	10.98 in (27.9 cm)
Depth	18.94 in (48.1 cm)
Net Weight	49.01 lb(US) (22.23 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery blocks per string	10
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery Voltage	120 V
RBC Quantity	1

Ordering and shipping details

GTIN	731304356196
Package weight(Lbs)	55.40 lb(US) (25.13 kg)

Packing Units

Package 1 Height	9.96 in (25.3 cm)
Package 1 width	11.54 in (29.3 cm)
Package 1 Length	19.49 in (49.5 cm)
Number of Units in Package 3	32

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------