



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	Installation guide
--------------------	--------------------

Physical

Color	Beige
Depth	15.98 in (40.6 cm)
Height	0.98 in (2.5 cm)
Product Weight	3.31 lb(US) (1.5 kg)
Width	95.98 in (243.8 cm)

Environmental

Ambient Air Temperature for Operation	-35...165 °F (-37...74 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...3000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	Non-condensing 0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	4.10 lb(US) (1.86 kg)
---------------------	-----------------------

Packing Units

Package 1 Height	2.01 in (5.1 cm)
Package 1 width	17.48 in (44.4 cm)
Package 1 Length	17.48 in (44.4 cm)

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------