




DATE	REV	ECN	APP'D. BY
1-13-15	Α7	10187	TRM
3-8-16	A8	10593	TRM
7-10-23	B0	12208/12209	JE


В

Α









ALL CENTERLINE DIMENSIONS ARE BASIC.

NOTES:

- 1. CONNECTOR MATERIALS: HOUSING: THERMOPLASTIC UL94 V-0 CONTACTS: COPPER ALLOY CONTACT PLATING: SELECTIVE GOLD IN CONTACT AREA SEE CHART FOR PART NUMBER
- 2. FOR PRODUCT SPECIFICATION SEE PR022-01
- 3. DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.

50 MICRO-INCHES [1.27um]	SS-641010-NF-50
30 MICRO-INCHES [0.76um]	SS-641010-NF
CONTACT PLATING IN MATING AREA	PART NUMBER

RoHS

THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	TITLE: TEN CO

a bel group

11118 Susquehanna Trail South Glen Rock, PA 17327-9199 (717) 235-7512

http://www.stewartconnector.com

TEN CONTACT, TEN POSITION, UNSHIELDED JACK, NON-FLANGE

THIS DRAWING AND THE SUBJECT MATTER SHOWN TH ARE CONFIDENTIAL AND THE PROPRIETARY PROPER STEWART CONNECTOR AND SHALL NOT BE REPRODU COPIED, OR USED IN ANY MANNER WITHOUT PRIOR W CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLE

VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PA

HEREON RTY OF	DRN BY:	QUI	^{DATE} 7–	15-	05
UCED, WRITTEN PATENTS	APPD BY:	DANNY	DATE 7-	15-	05
EASE TENTS/	DWG NO.	CT640067		REV.	В0

DIMENSIONS: INCHES [METRIC] UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1'

SHEET NO. 1 OF

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

AutoCAD