

P/N 36-651000-10 36-Pin SSOP-to-0.6 DIP Adapter

GENERAL SPECIFICATIONS

- PCB: FR-4, 0.062 [1.56] or 0.094 [2.39] thick
- PADS: bare Cu protected with Entek® by Enthone or Omikron® white Sn to eliminate co-planarity concerns and solder bridges
- MALE PINS: Brass 360 1/2-hard per UNS C36000, ASTM B16/B16M
- OPERATING TEMPERATURE: 221°F [105°C]
- MALE PIN PLATING: 200μ [5.08μ] Sn/Pb 93/7 per ASTM B579-73 over 100μ [2.54μ] Ni per SAE-AMS-QQ-N-290

MOUNTING CONSIDERATIONS

Standard thru-hole




CUSTOMIZATION: In addition to the standard products shown on this page, Aries specializes in custom design and production. Special materials, platings, sizes, and configurations can be furnished, depending on the quantity. **NOTE:** Aries reserves the right to change product general specifications without notice.

ORDERING INFORMATION

24-651000-10 24-651000-10-P = Panelized Version

ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: ± 0.005 [0.13] UNLESS OTHERWISE SPECIFIED CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS





Bristol, PA 19007-6810 USA
TEL (215) 781-9956 • FAX (215) 781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM