



Mallory Sonalert Products Inc.

Part #

PK-27A35EWBQ

Sales Outline Drawing

Revision

D

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Oscillation Frequency (Hz)	3500 ± 500
Operating Voltage (Vdc)	3 - 24
Rated Voltage (Vdc)	12
Current Consumption (mA/max)	15 at Rated Voltage
Sound Pressure Level (dB/min)	95 at 30cm at Rated voltage
Tone/Pulse Rate (Hz0	Constant
Operating Temperature (°C)	-40 ~ +70
Storage Temperature (°C)	-40 ~ +80
Housing	ABS 757 UL94HB plastic resin (Color: Black)
Lead Wires	24 AWG
Weight (Grams)	22
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant

