MALLORY Mallory Sonalert Products Inc.	Part #	PT-1140PEQ
Sales Outline Drawing	Revision	D

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

eations. Contact Maniory Sonaici	t to discuss your application.
Resonant Frequency (Hz)	$4000 \pm 500$
Operating Voltage (Vp-p/max)	20
Rated Voltage (Vp-p)	9.0
Current Consumption (mA/max)	7.0 at Rated Voltage
Sound Pressure Level (dB/min)	85 at 10cm at Rated voltage
Capacitance (pF)	12,000 ±30% at 120Hz
Operating Temperature (°C)	-20 ~ +60
Storage Temperature (°C)	-30 ~ +70
Housing	PBT1200 UL94HB plastic resin
	(Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	1.5
Condition by wave soldering (°C)	$260 \pm 5$ / within 5 sec
Condition by hand soldering (°C)	$350 \pm 20$ / within 5 sec
Options	For other options contact factory

## **NO CIRCUITRY**

**Dimensions:** (units: mm) ROHS Compliant

