

Specifications:

Voltage Rating (Vdc)	12 to 48
Frequency (Hz)	1600 $\pm$ 20%
Loudness (dB(A) @ 4ft)	82 to 102 (self adjusting)
Current Draw (Amps max)	0.6
Sound Pulse Rate (pps)	1 to 2
Operating Temperature (°C)	-40 to +85
Termination	8-32 UNC Studs
Housing	ABS, 10% Glass Filled, Black UL94V-0
Spike Protected	+100 / -400 Volts
Conforms to SAEJ994 (OCT 02) Standards	
Cross Reference	
ECCO	SA931
PRECO	1048
Weight (lbs.)	0.784

Dimensions: Inches (mm)