

CHERRY G84-4400

High performance right down to the smallest detail!



Models may vary from the image shown

Need a pointing device but space restrictions prevent you from using an extra mouse? The ultra-flat compact keyboard with built-in trackball is the perfect solution. The keyboard is optimally suited for 19-inch applications, slim-line PCs and laptops.

FUNCTION AND PERFORMANCE

- Individual keys with Gold Crosspoint contacts (ML technology)
- Designed for continuous usage - over 20 mill. confirmations per key
- High level of reliability and unique precision confirmation feeling
- Minimal space requirements
- Lightweight
- Can also be delivered without 'Windows® keys' (83 keys)
- Complete functions of a standard keyboard
- Can be used with the standard drivers of the operating system
- Ideal for 19" applications and mobile use

TECHNICAL DATA

Weight main product:	20 oz
Weight of product without packaging:	18.73 oz
Weight of product incl. packaging:	23.56 oz

Dimensions product without packaging: 14,57 in x 5,47 in x 0,77 in

Storage temperature: -4 °F - 140 °F

Working temperature: 32 °F - 104 °F

Product approvals:

- BSMI
- RCM
- CE
- cURus
- FCC
- ICES-003 (Canada)
- UKCA
- VCCI
- VDE

Operating system:

- Windows Vista or higher
- Windows XP
- Windows 7
- Windows 8
- Windows 10
- Windows 11

Scope of delivery:

- Manual
- Keyboard

Software support: CHERRY KEYS

Service life per key: 20 mio. actuations

Switching characteristics: tactile

Max. current consumption (mA) of keyboard: 24 mA

Keyboard format: Compact (75%)

N-Key Rollover: no

Anti-ghosting: no

Key encryption: no

Actuating force (cN): 50 cN

Key labeling: Laser etching

Palm rest: Palm rest not available

USB-Hub: no

Special key functions: CHERRY Key

Illumination: no

Status LEDs: in housing

Key technology: Mechanical

Switches: CHERRY ML

Keycap material: ABS

Model number: ML4400

Protection class: Standard

Warranty: 2 years warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

SKU / EAN / UPC	Protection class	Switches	Colour	Illumination	Layout
G84-4400LPBBE-2 EAN 4025112062643 UPC	Standard	CHERRY ML	black	no	BE (Belgium)
G84-4400 EAN UPC	Standard	CHERRY ML	black	no	CH (Switzerland)
G84-4400LPBDE-2 EAN 4025112062667 UPC	Standard	CHERRY ML	black	no	DE (Germany)
G84-4400LPBEU-2 EAN 4025112062698 UPC 840183601119	Standard	CHERRY ML	black	no	EU (USA+ €-Symbol)
G84-4400LPBFR-2 EAN 4025112062704 UPC	Standard	CHERRY ML	black	no	FR (France)
G84-4400LPBGB-2 EAN 4025112062711 UPC	Standard	CHERRY ML	black	no	GB (United Kingdom)
G84-4420LPBEU-2 EAN 4025112067174 UPC 840183601195	Standard	CHERRY ML	black	no	US (USA)
G84-4400LUBBE-2 EAN 4025112062841 UPC	Standard	CHERRY ML	black	no	BE (Belgium)
G84-4400 EAN UPC	Standard	CHERRY ML	black	no	CH (Switzerland)
G84-4400LUBDE-2 EAN 4025112062865 UPC 840183601126	Standard	CHERRY ML	black	no	DE (Germany)
G84-4400LUBEU-2 EAN 4025112062896 UPC 840183601140	Standard	CHERRY ML	black	no	EU (USA+ €-Symbol)
G84-4400LUBFR-2 EAN 4025112062902 UPC	Standard	CHERRY ML	black	no	FR (France)
G84-4400LUBGB-2 EAN 4025112062919 UPC 840183601157	Standard	CHERRY ML	black	no	GB (United Kingdom)

SKU / EAN / UPC	Protection class	Switches	Colour	Illumination	Layout
G84-4400LUBIT-2 EAN 4025112062926 UPC	Standard	CHERRY ML	black	no	IT (Italy)
G84-4400LUBPN-2 EAN 4025112084423 UPC	Standard	CHERRY ML	black	no	PN (PanNordic)
G84-4400LUBTQ-2 EAN 4025112075926 UPC	Standard	CHERRY ML	black	no	TQ (Turkey)
G84-4420LUBEU-2 EAN 4025112067921 UPC 840183601218	Standard	CHERRY ML	black	no	US (USA)
G84-4400 EAN UPC	Standard	CHERRY ML	light-grey	no	CH (Switzerland)
G84-4400LPBDE-0 EAN 4025112026386 UPC	Standard	CHERRY ML	light-grey	no	DE (Germany)
G84-4400LPBEU-0 EAN 4025112026362 UPC 840183601102	Standard	CHERRY ML	light-grey	no	EU (USA+ €-Symbol)
G84-4400LPBFR-0 EAN 4025112026867 UPC	Standard	CHERRY ML	light-grey	no	FR (France)
G84-4400LPBGB-0 EAN 4025112026850 UPC	Standard	CHERRY ML	light-grey	no	GB (United Kingdom)
G84-4400LPBRB-0 EAN 4025112037856 UPC	Standard	CHERRY ML	light-grey	no	RB (US / Cyrillic)
G84-4420LPBEU-0 EAN 4025112067167 UPC 840183601188	Standard	CHERRY ML	light-grey	no	US (USA)
G84-4400LUBBE-0 EAN 4025112049330 UPC	Standard	CHERRY ML	light-grey	no	BE (Belgium)
G84-4400 EAN UPC	Standard	CHERRY ML	light-grey	no	CH (Switzerland)

SKU / EAN / UPC	Protection class	Switches	Colour	Illumination	Layout
G84-4400LUBDE-0 EAN 4025112026881 UPC	Standard	CHERRY ML	light-grey	no	DE (Germany)
G84-4400LUBEU-0 EAN 4025112037849 UPC 840183601133	Standard	CHERRY ML	light-grey	no	EU (USA+ €-Symbol)
G84-4400LUBFR-0 EAN 4025112026904 UPC	Standard	CHERRY ML	light-grey	no	FR (France)
G84-4400LUBGB-0 EAN 4025112026898 UPC	Standard	CHERRY ML	light-grey	no	GB (United Kingdom)
G84-4400 EAN UPC	Standard	CHERRY ML	light-grey	no	IT (Italy)
G84-4400 EAN UPC	Standard	CHERRY ML	light-grey	no	TQ (Turkey)
G84-4420LUBEU-0 EAN 4025112067914 UPC 840183601201	Standard	CHERRY ML	light-grey	no	US (USA)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.