

CHERRY KC 4500 ERGO

Relaxed and comfortable through the whole day's work.



Models may vary from the image shown

Do you suffer from tense shoulders, cramp or other unpleasant symptoms when working on the computer? In many cases this is caused by incorrect posture.

Simple relief can be provided by an ergonomic keyboard such as the CHERRY KC 4500 ERGO. With its special design, your hands and arms take up a more natural position by themselves. This relieves your shoulders and back and your relaxed posture reduces stress. The extra-soft palm rest with memory foam prevents pressure points and lets you rest your hands comfortably.

The three feet allow you to raise the front of keyboard. This position is particularly comfortable when working in a standing position. The rubber feet also reliably prevent the keyboard from slipping – whether it's standing up or not.

An extra long cable with a USB plug allows you to connect the keyboard to the computer without any problems, even if the computer is under the desk, for example. The plug & play CHERRY KC 4500 ERGO is ready for use without any additional software. With its elegant colors and modern design, it looks great on any desk.

Once you've become used to the special design, typing is the same as on any other CHERRY keyboard: easy and uncomplicated.

Multimedia functions (volume up/down/off, next/

previous track, start/pause) are integrated in the F-keys. You can easily call them up by pressing the FN key at the same time.

To make your daily work even easier, the free CHERRY KEYS software offers many customization options. CHERRY KEYS allows quick access to apps, files, individual text modules or macros at the touch of a key.

FUNCTION AND PERFORMANCE

- The design of the USB keyboard supports an ergonomic posture when using the computer
- Curved keypad adapted to the movement of the hands and fingers for fatigue-free typing
- Soft padded palm rest with memory foam and high-quality PU leather
- Sturdy, fold-out feet on the underside for adjustable keyboard angle
- 1.8 m long, flexible cable for easy setup
- Additional commands such as volume up/down on the F buttons
- Configurable keys with optional, free CHERRY KEYS software

TECHNICAL DATA

Weight main product:	26 oz
Weight of product without packaging:	26.46 oz
Weight of product incl. packaging:	39.72 oz
Weight of master carton incl. content:	440.93 oz
Content of master carton (pieces):	10
Dimensions product without packaging:	17,95 in x 8,54 in x 1,38 in
Dimensions product incl. packaging:	18,74 in x 10,16 in x 1,57 in
Dimensions master carton:	19.29 in x 18.31 in x 11.14 in
Cable length:	5.91 ft
Storage temperature:	-4 °F - 140 °F

Working temperature:	32 °F - 104 °F
Product approvals:	<ul style="list-style-type: none"> • CE • cTÜVus • FCC • Windows Hardware Compatibility • China RoHS • UKCA
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none"> • Windows 7 • Windows 8 • Windows 10 • Windows 11
Scope of delivery:	<ul style="list-style-type: none"> • Manual • Keyboard
Reliability:	MTBF (90) > 80.000 Stunden
Software support:	CHERRY KEYS
Service life per key (in million strokes):	10 mio. actuations
Switching characteristics:	standard
Max. current consumption (mA) of keyboard:	10 mA
Keyboard format:	Full-size (100%)
Integrated metal plate:	no

N-Key Rollover:	no
Anti-ghosting:	no
Key encryption:	no
Internal memory:	no
Actuating force (cN):	55 cN
Actuating force tol.:	15 cN
Pre-Travel:	2,2 mm
Key labeling:	Pad Printing + UV coating
Palm rest:	Palm rest included
USB-Hub:	no
Special key functions:	<ul style="list-style-type: none"> • PC lock • Calculator • FN
Illumination:	no
Adjustable feet:	integrated
Status LEDs:	in housing
Key technology:	Rubberdome
Keycap material:	ABS
Model number:	JK-45
Protection class:	Standard
Warranty:	1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

SKU / EAN / UPC	Protection class	Colour	Illumination	Layout
JK-4500BE-2 EAN 4025112094941 UPC	Standard	black	no	BE (Belgium)
JK-4500CH-2 EAN 4025112093968 UPC	Standard	black	no	CH (Switzerland)
JK-4500CN-2 EAN 4025112098819 UPC	Standard	black	no	CN (China)
JK-4500DE-2 EAN 4025112093937 UPC	Standard	black	no	DE (Germany)
JK-4500ES-2 EAN 4025112096457 UPC	Standard	black	no	ES (Spain)
JK-4500EU-2 EAN 4025112093920 UPC 840183605810	Standard	black	no	EU (USA+ €-Symbol)
JK-4500FR-2 EAN 4025112093944 UPC	Standard	black	no	FR (France)
JK-4500GB-2 EAN 4025112093951 UPC	Standard	black	no	GB (United Kingdom)
JK-4500PN-2 EAN 4025112093975 UPC	Standard	black	no	PN (PanNordic)
JK-4501PN-2 EAN 4025112094804 UPC	Standard	black	no	
JK-4500DE-0 EAN 4025112102509 UPC	Standard	white-grey	no	DE (Germany)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.