










12	11	10	9	8	7	6	5	4	3	2	1
NOTES										DWG STATUS	
- ON MAIN VIEW ASSEMBLY 33285118 SHOWN (CODE A)										DATE	STG
- DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION										REV	N/P
ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY										CHG	ZONE
MATING PARTS: - 2 WAY 6.3 FEMALE CONNECTOR ASM DWG-NO.: 35153949 - FIXING SLIDE APTIV DWG-NO.: 33294397 (HT DWG-NO.: 17-1458-001-CS6) - BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CS6) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CS6) - PROTECTION CAP APTIV DWG-NO.: 35428682 (HT DWG-NO.: 17-2271-001-CS6)										REVISION HISTORY	
MATING TERMINAL SYSTEM: - 5.8 TERMINAL DWG-NO.: 10857383 MAX WIRE CROSS SECTION: 6.0MM ²										AUTH	DR
1	APTIV LOGO									APVD 1	APVD 2
2	MATERIAL NAME ACCORDING TO VDA 260									P.BAL P.NAJ M.GRU	
3	DATE INSERT									K.FAR M.GRU K.PIT	
4	TOOL CAVITY NUMBER									P.NAJ M.GRU	
5	INDEX REPLACEMENT INSERT										
6	PART CAVITY NUMBER										
7	MOVING DISTANCE OF SECONDARY LOCK										



				9		8		7		6		5		4		3			
				POSITION		1								2		3		4	
				NAME		HOUSING PANAL MOUNT								SECONDARY LOCK		SL SEAL		FIXING SEAL	
				MATERIAL		PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE		LSR 70 SHORE	
				COLOR:		BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN		REDDISH-BROWN	
PART-NO.:		33282970	33295516	33295350	33295348	33346024	33347366	33347365	33347364	33282489	33344854	33283927	33283926						
10	01	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	---	---	---		
8	01	CODE A	ALL PARTS V0 / 23,95	-	-	1	---	---	---	---	---	---	1	---	1	---	1		
3	01	CODE B		-	---	1	---	---	---	---	---	---	1	---	1	---	1		
4	01	CODE C		-	---	---	1	---	---	---	---	---	1	---	1	---	1		
5	01	CODE D		-	---	---	---	1	---	---	---	---	1	---	1	---	1		
0	01	CODE A	ALL PARTS NVO / 23,3	-	---	---	---	---	1	---	---	---	---	1	---	1	---		
1	01	CODE B		-	---	---	---	---	---	1	---	---	---	1	---	1	---		
2	01	CODE C		-	---	---	---	---	---	---	1	---	---	1	---	1	---		
3	01	CODE D		-	---	---	---	---	---	---	---	1	---	1	---	1	---		



MOUNTING BRACKET THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:	COLOR
-	PBT GF30 FR17	PBT GF30
1MM	35065351	35065358
1.5MM	35065364	35065366
2MM	35065367	35065368
2.5MM	33282490 / 151-02370	33344869 / 151-02371
3MM	33341422 / 151-02374	33344870 / 151-02375
3.5MM	33341423 / 151-02378	33344871 / 151-02379
4MM	35065369	35065353



DIM TO CHECK	DIMENSIONAL RANGE (MM)										CHART E1
	FROM TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400	
DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED										
THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	