







SYMBOL DEFINITION		
	TOTAL NO OF INSPECTIONS REQUIRED	9
	LAST NO. USED	10

MISSING SYMBOLS		DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD	APVD
		DATE	STG	REV	N/P	CHG						
2	3	5						35191210 WAS PE377692 AND RELEASED PART DRAWING; 35191211 WAS PE377693 AND RELEASED PART DRAWING; 35191212 WAS PE377694 AND RELEASED PART DRAWING	440173	SNS	SNS	DAB
								DIM #4 WAS 10±0.1; ADDED DATUMS AND PROFILE TOLERANCE; ADDED DIM #5-8; ADDED NOTE 8 AND 9; REMOVED DIM #2-3; REMOVED NOTE 6	440587	AN	SNS	DAB
								ALL PARTS - REVISED MATERIAL COLOR	441241	AN	SNS	ERM
								REMOVED NO PART AVAILABLE LINE ADDED TOLERANCE ACCEPTED TABLE	445398	YS	YS	MA
								DELETED DIM#5 AND ADDED DIM#9 #10	445398	YS	MA	YS



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- PARTS MUST BE FREE OF DUST, DIRT, CARDBOARD FIBERS, OR ANY PARTICULATE THAT MAY CAUSE FIT OR FUNCTION CONCERN. PARTS MUST BE PACKED IN SEALED PLASTIC BAGS.
- PARTS MUST BE MADE FROM VIRGIN MATERIAL ONLY.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
SHOWN ON TAXI 35228534 AND 35228536
- PARTS SHOWN ON THIS DRAWING ARE USED IN ASSEMBLIES SHOWN ON TAXI 35228533 AND 35228535.
- PARTS ARE TO BE PACKAGED IN SEALED PLASTIC BAGS. GROSS WEIGHT INCLUDING CARTON IS NOT TO EXCEED 30 POUNDS.
- FOR TOOL FIXERS, TOOL MOVEMENTS AND RE-PPAP REVIEW TQD DRAWINGS FOR CRITICAL DIMENSION. DIM #5 & 228 MUST COMPLY.
- FOR PROFILE INSPECTION DETAILS SEE TQD.

10		26.37
9		22.52
4		10.145
DIMENSION NUMBER	MINIMAL VALUE	MAXIMAL VALUE
DIMENSIONS OUT OF TOLERANCE RANGE BUT ACCEPTED FOR CHN TOOL 35191210-RL-B-C002		

35191210	02	-	SILICONE COMPOUND - BLU	4.486	6.4-7.2	5.3
35191211	02	-	SILICONE COMPOUND - GRA	4.318	7.9-8.7	6.8
35191212	02	-	SILICONE COMPOUND - RED	4.101	9.4-10.4	8.4
PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOLUME (CM³)	CABLE O.D (MM)	A± 0.1

DIMENSIONAL RANGE (MM)											
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	CHART E1
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
ANGULAR TOLERANCE ±2°											

4	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (CM³)	
SEE CHART	
DISTR CODE	
D	
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE QM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX

• APTIV •	
CONNECTION SYSTEMS	
Anting, China	
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	DATE
APVD1 S. SUBRAMANIAN	21JN18
APVD2 S. SUBRAMANIAN	21JN18
APVD3 DARIEN AGUILAR	21JN18
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI SEAL CBL 1W PWR PACK	
DRAWING NUMBER	
35228537	
SIZE	SCALE
A1	5:1
FRAME NO	SHEET NO
1 OF 1	1 OF 1
STG	REV
R	03
N/P	AB