

Industrial Power Strip Metal, Lighted Power Switch, 6-Outlet, 6 ft. (1.8 m) Cord

MODEL NUMBER: **6SP**



Highlights

- 6 outlets
- 6-ft. (1.83 m) cord
- 13.7-in. overall length
- Lighted master power switch

Package Includes

- 6SP Power Strip
- Warranty information
- Instruction manual

Description

The 6SP Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R output receptacles with 1.625-inch center-to-center spacing, six-foot (1.8 meters) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Cabled, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes 6SP ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.625-in. center-to-center outlet spacing
- Lighted power switch
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity with circuit breaker
- 6-ft. (1.83 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332103383
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V



Powering Business Worldwide

TRIPP LITE
SERIES

Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
Outlet Spacing	1.625 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
PHYSICAL	
Color	Gray
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17mm
Outlets Measurement (Center to Center)	1.62 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.50 x 3.60 x 6.10
Shipping Dimensions (hwd / cm)	36.83 x 9.14 x 15.49
Shipping Weight (lbs.)	2.22
Shipping Weight (kg)	1.01
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Outlet Spacing	1.625 in.



Powering Business Worldwide

TRIPP LITE
SERIES

Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.