

8-Port VGA over Cat5/6 Splitter/Extender, Box-Style Transmitter for Video/Audio, Up to 1000 ft. (305 m), TAA

MODEL NUMBER: **B132-008A-2**



Works with Tripp Lite's B132-Series receivers to transmit a VGA + audio signal to 9 sets of displays and speakers (8 remote, 1 local) up to 1,000 ft. away. Ideal for digital signs, trade shows and classrooms.

Features

Transmits a Single High-Definition VGA + Audio Signal to 9 Sets of Displays/Speakers

- Ideal for applications where the video source is located farther than conventional cables allow or that require multiple displays connected to one source
- Splits one VGA + audio signal into 9 separate signals (8 remote, 1 local)
- B132-100A or B132-100A-WP-1 remote receiver required for each remote signal

Daisy-Chain Units to Reach More Remote Displays

- Daisy-chain up to 6 units to extend the original audio/video signal to as many as 49 displays (48 remote, 1 local)
- Connects to next link in chain with one Cat5/Cat6 cable, such as 24 AWG solid-wire N022-01K-GY (Cat5e) or N222-01K-GY (Cat6) cable
- Add up to 3 B132-110A remote repeaters to each channel to extend signal range or add displays

Extends Signals Up to 1,000 ft.

- Extends a 1920 x 1440 (60 Hz) signal up to 500 ft. away from the audio/video source
- Extends a 1024 x 768 (60 Hz) signal up to 1,000 ft. away from the audio/video source
- Supports high-quality audio

Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Connects quickly to source and displays with VGA cable, such as P504-Series
- LEDs indicate at a glance when the unit is receiving power and a VGA signal from the source
- Included mounting hardware lets you install the unit on a wall, rack or pole

Highlights

- Requires remote receivers (sold separately)
- Extends 1024 x 768 @ 60 Hz audio/video signal up to 1,000 ft.
- Extends 1920 x 1440 @ 60 Hz audio/video signal up to 500 ft.
- Daisy-chain up to 6 units to extend signal to 49 displays
- Plug and play—no software or drivers to install

Package Includes

- B132-008A-2 8-Port VGA + Audio over Cat5/6 Extender Splitter
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 2A)
- VGA + audio daisy-chain cable, 1 ft.
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332190246
Product Type	Splitter; Extender Kit
Technology	VGA/SVGA; Stereo Audio; Cat5/5e; Cat6
Host Connector	HD15 (FEMALE)
VIDEO	
Max Supported Video Resolution	1920 x 1440 @ 60Hz
Max 720P Range (ft)	500
Max 1080P Range (ft)	500
Max 1280 x 720 (720p) Range (ft)	500
Max 1920 x 1080 (1080p) Range (ft)	500
Max 1920 x 1200 Range (ft)	500
Transmitter Video Input	VGA
Transmitter - Number of Video Outputs	8
Transmitter - Local Display Output	VGA
Range Extension using other Tripp Lite product	1000 ft. @ 1024 x 768 (60Hz) 500 ft. @ 1920 x 1440 (60Hz)
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Other Tripp Lite product used to extend range	B132-110A
HDR Support	No
3D Video Supported	No
Maximum Signal Range (ft)	1000
Maximum Signal Range (m)	305
Maximum Signal Range Details	1000 ft @ 1024 x 768 (60Hz) 500 ft @ 1920 x 1440 (60Hz)
AUDIO	
Audio Input	3.5mm
Audio Specification	Stereo Audio
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America



Powering Business Worldwide

TRIPP LITE
SERIES

AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
AC Power Adapter Output Specs (V / A)	5V / 3A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.38
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A, 4.5 ft.
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	8
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	3.5MM (FEMALE)
Side B - Connector 1	(8) RJ45 (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	3.5MM (FEMALE)
Input x Output	1 x 8
Daisy-chainable / Cascadable	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Green); Orange (Activity, EDID)
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Number of Displays	8
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-02
Form Factor/Mounting Options	Box; Wall-mount
Shipping Dimensions (hwd / in.)	2.20 x 13.90 x 6.50
Shipping Dimensions (hwd / cm)	5.59 x 35.31 x 16.51



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (lbs.)	3.90
Shipping Weight (kg)	1.77
Unit Dimensions (hwd / in.)	1.200 x 9.300 x 3.900
Unit Dimensions (hwd / cm)	3.05 x 23.6 x 9.91
Unit Packaging Type	Box
Unit Weight (lbs.)	1.5
Unit Weight (kg)	0.68
Housing	Metal
Mounting Details	Wallmount
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Relative Humidity	10% to 90% RH, Non-Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	1000
Max 480P Range (ft)	1000
Max 1440 x 900 Range (ft)	500
Max 1080i Range (ft)	500
Max 1920 x 1440 Range (ft)	500
Max 480i Range (ft)	1000
Max 640 x 480 Range (ft)	1000
Max 800 x 600 Range (ft)	1000
Max 1600 x 1200 Range (ft)	500
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
USB Extension Support	No
PORT EXPANSION	
Daisy-chainable or Cascadable	Cascadable
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
MST Support	No



Powering Business Worldwide

TRIPP LITE
SERIES

Built-In Equalizer	No
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
Product Compliance	RoHS; REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.