

1-Port USB over Cat5/Cat6 Extender Kit - Plug and Play, International Plug Adapters, 164 ft. (50 m), TAA

MODEL NUMBER: B203-101-PNPINT



Connects your home/office PC or laptop to a webcam, printer, hard drive or other USB peripheral located up to 164 ft. (50 m) away.

Features

Connects Your Computer or Laptop to a USB Device up to 164 ft. (50 m) Away

This plug-and-play extender kit is ideal for connecting your home or office computer's USB-A port to a printer, webcam, external hard drive or other USB peripheral located up to 164 feet (50 meters) away. The B203-101-PNPINT includes a local transmitter and a remote receiver. It sends USB signals over user-supplied Cat5e/6 cabling (such as N202-Series Cat6 Ethernet cables).

With Great Distance Comes Great Flexibility

By extending the USB connection beyond the standard 16-foot (4.9 meters) distance limitation to 164 feet (50 meters), the B203-101-PNPINT provides workstation flexibility to place your computer and its connected USB peripheral where they are best suited, even in separate rooms. This extender kit supports USB 2.0 data transfer rates up to 480 Mbps and is backward compatible with USB 1.1 technology, allowing you to connect legacy devices. No network connectivity is needed.

Built-In USB Cable Offers a Fast, Easy Plug-and-Play Connection

Just connect the transmitter's USB cable to your computer's USB-A port, connect a USB peripheral to the receiver's USB-A port, and connect the two units with Cat5e/6 cable (sold separately). No drivers or other software is needed. The included external power supply connects to the receiver. It comes with four international plug adapters (North America, United Kingdom, Europe, Australia), so you can connect to a wall outlet, UPS, PDU or surge protector almost anywhere.

TAA-Compliant for GSA Schedule Purchases

The B203-101-PNPINT is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Supports USB 2.0 speeds up to 480 Mbps to ensure reliable data transfers
- Includes 4 international plug adapters for connecting to almost any electrical outlet
- Widely compatible transmitter/receiver kit works with all major operating systems
- Plug-and-play operation with no software required for easy, immediate installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Computer or laptop with USB-A port
- Any major operating system
- Cat5/5e/6/6a cabling

Package Includes

- Transmitter
- Receiver
- External power supply (Input: 100-240V, 50/60 Hz, 0.35A; Output: 5V 2A)
- (4) International plug adapters (North America, U.K., Europe, Australia)
- Owner's manual

Specifications

OVERVIEW

UPC Code

037332271563



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	USB 2.0 (High Speed)
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.38
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	100-240V, 50/60Hz, 0.35A
Input Current	5V 2A
Bus Powered	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
POWER	
Power Source Type	AC Adapter
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB A (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Connector Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	Plastic
Rackmountable	No
Receiver Unit Dimensions (hwd / cm.)	2.4 x 6.1 x 5.18
Receiver Unit Dimensions (hwd / in.)	0.94 x 2.4 x 2.04
Receiver Unit Weight (kg)	0.08
Receiver Unit Weight (lbs.)	0.17
Shipping Dimensions (hwd / in.)	2.20 x 6.20 x 8.50



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	5.59 x 15.75 x 21.59
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Transmitter Unit Dimensions (hwd / cm.)	2.4 x 5.5 x 3.45
Transmitter Unit Dimensions (hwd / in.)	0.94 x 2.17 x 1.36
Transmitter Unit Weight (kg)	0.08
Transmitter Unit Weight (lbs.)	0.17
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Relative Humidity	0-85% non-condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
Recommended Category Cable	Cat6
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CCC; CE; DOE; FCC; GS; LPS; TUV; UL; cUL
Product Certifications	NOM (Mexico)
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.