

External 240V 3U Rack/Tower Battery Pack Enclosure + DC Cabling for select UPS Systems (BP240V10RT3U)

MODEL NUMBER: BP240V10RT3U



Need more runtime? The BP240V10RT3U external battery pack extends the runtime of compatible Tripp Lite UPS Systems and has a rear connector for daisy-chaining multiple battery packs together to achieve an even longer runtime. Installation is quick, simple and versatile—the battery pack can be adapted to rackmount (3U), tower or stack form factors.

Description

BP240V10RT3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 240V rack-mount and tower UPS systems. Includes heavy-gauge cabling with high-current DC connector for safe, simple installation. Included daisy-chain connector enables the connection of additional compatible 240V external battery packs to the host UPS. Included mounting accessories support 3U rack-mount installation in 4-post racks. Options for 2-post center-mounting and upright tower installation available.

Compatible with SU6000RT3U, SU6000RT3UHV, SU8000RT3U, SU8000RT3U1TF, SU8000RT3UG, SU8000RT3UHW, SU8000RT3UN50, SU8000RT3UN50TF, SU10000RT3U, SU10000RT3U2TF, SU10000RT3UG, SU10KRT3U, SU10KRT3UHV, SU10K3/1INTPM, SU16KRT, SU16KRT-1TF, SU16KRT8, SU16KRTG, SU16KRTHW, SU20KRT, SU20KRT-1TF, SU20KRT8, SU20KRTG, SU20KRTHW and other UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible 240V DC UPS systems
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 240V external battery packs to the host UPS
- Included mounting brackets support rack-mount installation in 4-post racks using only 3 rack spaces (3U)
- 2POSTRMKITHD option supports balanced two-point center-mounting in 2-post equipment racks
- 2-9USTAND option enables upright tower placement

Specifications

Highlights

- Extends the runtime of expandable 240V DC UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rack-mount installation; 4-post installation accessories included
- Options for 2-post rack-mount and tower installation available

Package Includes

- BP240V10RT3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual



Powering Business Worldwide



UPC Code	037332115843
INPUT	
Input Phase	Single-Phase
BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	240
UPS Connection	Detachable cable with UPS specific DC connector (91.4 cm length, 6 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Material of Construction	Steel
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2 post rackmount); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems)
Minimum Required Rack Depth (cm)	71.12
Minimum Required Rack Depth (inches)	28
Shipping Dimensions (hwd / in.)	11.50 x 23.00 x 33.00
Shipping Dimensions (hwd / cm)	29.21 x 58.42 x 83.82
Shipping Weight (lbs.)	184.00
Shipping Weight (kg)	83.46
Unit Dimensions (hwd / in.)	5.250 x 17.500 x 25.000
Unit Dimensions (hwd / cm)	13.34 x 44.45 x 63.5
Unit Weight (lbs.)	158.70
Unit Weight (kg)	71.99
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty



Powering Business Worldwide



Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.