

DataShield Serial In-Line Surge Protector, DB9

MODEL NUMBER: DB9



Highlights

- Complete serial port (DB9) surge protection
- Protects against the effects of electrostatic discharge

Package Includes

- 1 DB9 Surge Suppressor

Is your DB9 serial connection protected? If not, your equipment is vulnerable to damage and performance problems. Surges and line noise don't just affect the power line; they can enter your equipment on any connection. So protect your DB9 serial equipment with the DataShield™ DB9 In-Line Surge Suppressor. It's the ideal choice for protecting PCs, printers, modems and anything with a DB9 connection.

Description

This DB9 offers dataline surge suppression for DB9 serial ports of data terminal and data communications equipment, including PCs, printers, modems and more. User-configurable for use with male or female captive DB9 ports. Offers protection on all nine lines, plus D shell chassis. Convenient DB9 input and output connects directly to the protected port, obtaining a ground outlet from the computer chassis. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges away from network interface connections. Network surge suppressors reduce blown interface cards, garbled transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground.

Features

- DB9 protects 9 pin serial connections for dataline surge suppression of data terminal, data communications equipment and PCs, printers, modems and more
- Reversible for use with male or female captive DB9 ports
- Offers protection on all 9 data lines, plus D shell chassis
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

Specifications

OVERVIEW	
UPC Code	037332010834
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Cord Length (ft.)	0



Powering Business Worldwide

TRIPP LITE
SERIES

Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	340
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	1-9 & Chassis
Telephone/DSL Protection	No
PHYSICAL	
Housing Color	Light Gray
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	5.00 x 3.00 x 2.00
Shipping Dimensions (hwd / cm)	12.70 x 7.62 x 5.08
Shipping Weight (lbs.)	0.16
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	0.640 x 1.380 x 2.850
Unit Weight (lbs.)	0.34
Unit Weight (kg)	0.15
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.