

Isobar 4-Outlet 230V Surge Protector, Detachable 6 ft. (1.83 m) Cord, 680 Joules, Metal Housing

MODEL NUMBER: **EURO-4**



Premium protection for valuable electronics against dangerous surges, spikes and line noise that can damage equipment or destroy data. Recommended for home, corporate, retail, telecom and industrial applications.

Description

Premium protection for home, corporate, retail, telecom and industrial applications, the EURO-4 Isobar® 4-Outlet 230V Surge Protector features a surge protection rating of 680 joules to defend your sensitive electronics against surges and spikes.

The EURO-R features four widely spaced C13 outlets, which are arranged in two exclusive isolated filter banks that prevent equipment connected to one bank from interacting with equipment connected to the other. These internal barriers also prevent disruptive line noise from causing A/V distortion, computer lock-ups, data errors and similar problems. Large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors remove EMI/RFI interference and prevent system crashes, reboots and performance problems.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the EURO-4 protects all three, covering two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

An integrated 9A circuit breaker protects all outlets and shuts down connected equipment in the event of an overload. A lighted on/off switch provides one-touch control over connected components. A C14 inlet accepts a variety of detachable power cords, such as the included 6-ft. (1.83 m) C13 cable. An all-metal housing ensures long life and durability.

Features

680-Joule Surge Protection for Home or Office Electronics Protects your A/V components, network hardware, retail displays, appliances, power tools and other electronics against surges and spikes
Recommended for home, corporate, retail, telecom and industrial applications requiring AC line protection
Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Exceeds IEEE 587 Category A and B surge suppression specifications

4 Outlets Accept Wide Range of Electronic Devices 4 C13 outlets
Outlets accommodate up to 2 transformers without blocking other outlets

Isolated Filter Banks Provide Extra Protection Outlets arranged in exclusive isolated filter banks to limit noise interaction among connected equipment
Blocks disruptive EMI/RFI line noise that can cause equipment damage or data loss
Combines large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and metal oxide varistors to block interference

Premium Safety Features Lighted on/off switch provides one-touch control over connected equipment
Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated,

Highlights

- 4 C13 outlets in exclusive isolated filter banks
- 680-joule surge protection rating
- Durable metal housing designed for tough environments
- 9A resettable circuit breaker prevents dangerous overloads
- Detachable 6-ft. (1.83 m) C13-to-C14 power cord

Package Includes

- EURO-4 Isobar 4-Outlet 230V Surge Protector, Metal Housing
- Detachable C13-to-C14 power cord, 6-ft. (1.83 m)
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

preventing equipment damage and indicating replacement is required

Fits Effortlessly Into Your Workstation Detachable 6-ft. (1.83 m) C13 power cord reaches nearby outlets C14 inlet accepts wide variety of power cords to match country or site-specific wall outlets Keyhole slots on bottom panel provide convenient wall or desk mounting options Metal housing designed for long life

Specifications

OVERVIEW	
UPC Code	037332010049
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Maximum Surge Amps	15000
Input Plug Type	IEC-320-C13
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) C13
Circuit Breaker (amps)	9
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Two position orange illuminated on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	680
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes, ferrite rod-core inductors and VHF capacitors.
EMI / RFI Filtering	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Isolated Filter Banks	Yes
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Metal
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between horizont tabs = 162.13 mm; Distance between vertical tabs = 58.17 mm
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 53mm; Distance between vertical outlets = 38.10mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	9.50 x 2.60 x 5.80
Shipping Dimensions (hwd / cm)	24.13 x 6.60 x 14.73
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
Unit Dimensions (hwd / in.)	2.500 x 7.000 x 3.500
Unit Dimensions (hwd / cm)	8.9 x 17.8 x 6.4
Unit Weight (lbs.)	2
Unit Weight (kg)	0.91
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1449
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.