



Powering Business Worldwide

USB / FireWire® - FireWire PC Device to PC Device Gold Cable

MODEL NUMBER: **F005-006-R**

Description

Tripp Lite's new Firewire series is a perfect compliment to your connectivity solutions. This 6 ft. IEEE-1394a Firewire cable has 6-pin male to 6-pin male connectors supports data transmission of 100~400Mbps and is used most commonly to connect a PC device to a PC device. Firewire cables have gold-plated connectors and gold-plated copper contacts for superior conductivity. Premium double-shielded cable with both a braid and a foil shield to virtually eliminate crosstalk and reduce EMI/RFI interference. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. clamshell retail package.

Features

- All Tripp Lite Firewire (IEEE 1394a) cabling includes superior foil shielding for reliable error-free data communications.
- Firewire cable meets IEEE 1394a standards as set by the institute of electrical and electronic engineers.
- Premium quadruple-shielded cables with tinned copper braid and aluminum
- Mylar foil on each twisted pair as well as on the cable as a whole.
- Gold plated connectors provide superior conductivity.
- Supports data transmission of 100~400Mbps
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Highlights

- Premium quadruple-shielded cables with tinned copper braid and aluminum mylar foil on each twisted pair as well as on the cable as a whole
- Gold plated connectors provide superior conductivity
- Retail packaging

System Requirements

- Two Firewire IEEE 1394 devices each with 6 Pin Female connectors.

Package Includes

- 6-ft. 6Pin to 6Pin Firewire 1394 device cable

Specifications

OVERVIEW	
UPC Code	037332011978
CONNECTIONS	
Side A - Connector 1	6 PIN (MALE)
Side B - Connector 1	6 PIN (MALE)
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	6.50 x 5.75 x 2.00
Shipping Dimensions (hwd / cm)	16.51 x 14.60 x 5.08
Shipping Weight (lbs.)	0.03
Shipping Weight (kg)	0.01
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.