

Cat6/Cat5e 110 Style Punch Down Keystone Jack - Blue, 25-Pack, TAA

MODEL NUMBER: N238-025-BL



Highlights

- 25-Pack
- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA CAT6 connecting hardware specifications.
- Dual-color coded labeling made for both 568A and 568B (258A) wiring schemes.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat6/Cat5e 110 Punch Down Keystone Jack - Blue, 25-Pack
- Termination Caps (x25)

Description

This Cat6/Cat5e 110-Style Punch-Down Keystone Jack provides maximum flexibility for any UTP Ethernet environment. Ideal for Cat5e cabling environments, the jack also meets UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test for Cat6 cabling installations. The uniquely patterned printed circuit board construction is designed to meet Cat6 250 MHz performance, and is fully compliant with EIA/TIA Cat6 connecting hardware specifications. With its compact casing, it fits into any conventional face plate, outlet box or panel. It also features dual-color-coded labeling made for both 568A and 568B (258A) wiring schemes.

UTP Cat6 22-24 AWG solid cable

Features

- 25-Pack
- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA Cat6 connecting hardware specifications
- Dual-color coded labeling made for both 568A & 568B (258A) wiring schemes
- Compact casing fits into any conventional face plate, outlet box, or panel
- UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test
- Uniquely patterned, printed circuit board designed to meet Cat6 performances
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332187840
Product Type	RJ45 Keystone Jack
Technology	Cat5/5e; Cat6
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PHYSICAL	
Color	Blue
Connector Color	Blue
Shipping Dimensions (hwd / in.)	7.01 x 7.87 x 0.50
Shipping Dimensions (hwd / cm)	17.81 x 19.99 x 1.27
Shipping Weight (lbs.)	0.48
Shipping Weight (kg)	0.22
Unit Dimensions (hwd / in.)	7.010 x 7.870 x 0.500
STANDARDS & COMPLIANCE	
Product Certifications	UL 1863; UL 2043
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.