

PDU Power Cord, C13 to C14 - 13A, 250V, 16 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P004-003-13A



Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 3 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to three feet. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- Adds 3-ft. (0.91 m) to your existing power connection to provide flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, servers and monitors to a PDU up to 3 ft. away in your data center
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-003-13A C14 Male to C13 Female Power Cable, 3 ft., Black

Specifications

OVERVIEW	
UPC Code	037332180445
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.