

## Power Cord Adapter, NEMA L5-20R to NEMA 5-20P - Heavy-Duty, 20A, 120V, 12 AWG, 8.66-in. (21.99 cm), Black

MODEL NUMBER: P044-06I



L5-20R to 5-20P heavy-duty power adapter transforms a NEMA 5-15/20R straight-blade outlet to a locking L5-20R outlet.

### Features

**Heavy-Duty Power Adapter Connects Devices That Require a Heavy-Gauge Connection** This heavy-duty adapter features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The six-inch power adapter transforms a NEMA 5-15/20R straight-blade outlet into a locking L5-20R outlet. It is also a recommended replacement or upgrade of a standard power cord provided by the device's manufacturer.

**Locking L5-20R Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking NEMA L5-20R connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking adapter is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

## Specifications

| OVERVIEW                    |                  |
|-----------------------------|------------------|
| UPC Code                    | 037332139115     |
| Device Compatibility        | Server; UPS; PDU |
| Country/Region              | North America    |
| INPUT                       |                  |
| Maximum Input Amps          | 20               |
| Voltage Compatibility (VAC) | 125              |
| CONNECTIONS                 |                  |

### Highlights

- 8.66 in. adapter allows easy transition to L5-20R outlet with no electrician needed
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking connector maintains secure link to avoid loss of power and costly downtime

### Applications

- Transform a non-locking outlet into a locking outlet to prevent a power loss due to accidental disconnection
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P044-06I L5-20R to 5-20P Heavy-Duty Power Adapter, 8.66 in., Black



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                             |
|--------------------------------------|-----------------------------|
| Side A - Connector 1                 | NEMA 5-20P                  |
| Side B - Connector 1                 | NEMA L5-20R                 |
| <b>PHYSICAL</b>                      |                             |
| Plug Color                           | Black                       |
| Cable Jacket Color                   | Black                       |
| Cable Jacket Material                | PVC                         |
| Cable Jacket Rating                  | VW-1                        |
| Power Cord Jacket Type               | SJT                         |
| Cable Outer Diameter (OD)            | 11mm                        |
| Number of Conductors                 | 3                           |
| Wire Gauge (AWG)                     | 12                          |
| Wire Gauge (OD - mm <sup>2</sup> )   | 3.31                        |
| Cable Length (ft.)                   | 0.72                        |
| Cable Length (m)                     | 0.22                        |
| Cable Length (cm)                    | 21.99                       |
| Shipping Dimensions (hwd / in.)      | 10.00 x 7.00 x 0.10         |
| Shipping Dimensions (hwd / cm)       | 25.40 x 17.78 x 0.25        |
| Shipping Weight (lbs.)               | 0.40                        |
| Shipping Weight (kg)                 | 0.18                        |
| <b>ENVIRONMENTAL</b>                 |                             |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range             | 10% to 65% RH               |
| Storage Humidity Range               | 10% to 65% RH               |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                             |
| Antibacterial                        | No                          |
| Angled Plug                          | No                          |
| High Voltage                         | No                          |
| Locking Plug                         | No                          |
| Coiled Power Cord                    | No                          |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                             |
| Product Certifications               | cUL Listed; UL Listed       |
| Product Compliance                   | RoHS                        |

WARRANTY & SUPPORT

|                                        |                           |
|----------------------------------------|---------------------------|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |
|----------------------------------------|---------------------------|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.