

China Computer Power Cord, GB 15934-2008 to C13 - 10A, 250V, 17 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P055-010-CHN1



C13 to GB 15934-2008 power cord transforms a C14 plug into a GB 15934-2008 plug for connecting to a grounded AC power outlet in China.

Features

C13 to GB 15934-2008 Power Cord Connects Servers and Other Network Devices This GB 15934-2008 to C13 Chinese computer power cord with molded ends is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a GB 15934-2008 grounded wall outlet or replace or upgrade a worn-out or lost Chinese power cable. The 10-ft. (3.05 m) (3-meter) length allows you great flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332232656
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	China
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	GB 15934-2008
Side B - Connector 1	IEC-320-C13
PHYSICAL	

Highlights

- C13 to GB 15934-2008 cable for powering computers, servers and other network devices
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing Chinese power cable

Applications

- Connect devices like computers, servers and printers to an outlet up to 3 m away in a hotel room or conference room in China
- Transform a C14 plug into a GB 15934-2008 plug with no electrician needed
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P055-010-CHN1 C13 to GB 15934-2008, China Computer Power Cord, 10-ft. (3.05 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	PVC
Cable Outer Diameter (OD)	7.0mm
Number of Conductors	3
Wire Gauge (AWG)	17
Wire Gauge (OD - mm ²)	1.15
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.80 x 8.86 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 22.50 x 1.27
Shipping Weight (lbs.)	0.65
Shipping Weight (kg)	0.29
ENVIRONMENTAL	
Operating Temperature Range	23° to 140°F (-5° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.