

European Computer Power Cord, C5 to Schuko, 2.5A, 250V, 16 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P058-006



C5 to Schuko EU power cord connects your notebook computer or laptop with a 3-slot C6 power inlet to a Schuko outlet.

Features

European Computer Power Cord Connects Notebook Computers to a Schuko AC Outlet This C5 to Schuko power cord is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other Schuko outlet. It is also a durable replacement for a worn-out or lost laptop power cord. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332153647
Device Compatibility	Laptop; Computer; UPS; PDU
Country/Region	Europe
INPUT	
Maximum Input Amps	2
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG
Side B - Connector 1	IEC-320-C5
PHYSICAL	

Highlights

- EU power cable recommended for powering notebooks and laptops with C6 inlets
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable

Applications

- Connect a laptop or notebook computer to a PDU up to 6 ft. (1.8 m) away in your workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

Package Includes

- P058-006 C5 to Schuko, European Computer Power Cord, 6 ft. (1.8 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.50 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	24.13 x 18.03 x 1.27
Shipping Weight (lbs.)	0.46
Shipping Weight (kg)	0.21
Unit Dimensions (hwd / in.)	9.500 x 7.100 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.