

Keyspan Mini DisplayPort to DisplayPort Cable Adapter, Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P139-06N-DP



Highlights

- Converts Mini Displayport on a MAC to Displayport Female
- Connect Displayport enabled monitor to a MAC computer
- Supports resolutions up to 2560 x 1600 @ 60Hz

Package Includes

6-inch Mini Displayport Male to Displayport Female Adapter

Features

- Connect a Displayport enabled Monitor to a MAC Mini-Displayport video port
- Plug and Play - no drivers or setup needed
- Displayport 1.1a Compliant
- HDCP Compliant
- Supports resolutions up to 2560 x 1600 @ 60Hz

Specifications

OVERVIEW	
UPC Code	037332161277
Product Type	Video Adapter
Technology	DisplayPort
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
PHYSICAL	
Color	White
Cable Jacket Color	White
Cable Length (ft.)	0.5
Cable Length (m)	0.15



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	0.25 x 0.25 x 6.50
Shipping Dimensions (hwd / cm)	0.64 x 0.64 x 16.51
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.