

HDMI Right Angle Up Adapter/Coupler (M/F), 4K @ 60Hz

MODEL NUMBER: **P142-000-UP**



Highlights

- Use in tight spaces where cables would not ordinarily fit
- Saves wear and tear on equipment ports and cable ends

System Requirements

- Video equipment with HDMI video out ports

Package Includes

- HDMI Male to Female Right Angle adapter

Description

The 90-degree angle of this adapter allows you to reposition the HDMI jack for better access where space is tight. This adapter also offers a great way to protect your HDMI cables and equipment from strain and damage, since HDMI cables have relatively small connectors and jacks that must bear the brunt of the cable's weight. The plug-and-play design makes installation a breeze. The P142-000-UP Right Angle HDMI Adapter features gold-plated connectors for optimal signal transmission quality. Provides clean, uncompressed digital signals. Supports video resolution up to 4K x 2K (3840 x 2160) @ 60Hz.

Features

- HDMI Male Plug
- HDMI Female Jack
- One inch deep when plugged into video port
- Supports video resolution up to 4K x 2K (3840 x 2160) @ 60Hz.

Specifications

OVERVIEW	
UPC Code	037332164698
Product Type	Video Adapter
Technology	HDMI
CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (MALE)
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Shipping Dimensions (hwd / in.)	5.30 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.46 x 9.91 x 1.27
Shipping Weight (lbs.)	0.03
Shipping Weight (kg)	0.01
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.