

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 25 ft. (7.62 m)

MODEL NUMBER: P560-025



Description

This DVI Dual-Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. Note: Review your monitor manufacturer's specifications for a stated maximum DVI cable length. While many monitors only support a five-meter (16-foot) DVI cable, simply adding a B120-000 DVI Extender will guarantee full digital signal strength at any length up to 150 feet (45.7 meters). Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual or Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars drain off extraneous electrical interference.

Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI
- Dual Link digital signaling for transmission speeds to 9.9Gbps and 2560 x 1600 resolution
- Meets DVI DDWG Standard
- PC and Mac compatible
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors
- Check monitor manufacturers cable length specs - may need B120-000 DVI Extender

Specifications

OVERVIEW	
UPC Code	037332138804
Product Type	Passive Cable
Technology	DVI
Cable Type	Passive
CONNECTIONS	

Highlights

- For use with Dual or Single TMDS Link specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Check monitor manufacturers cable length specs - may need B120-000 DVI Extender

System Requirements

- Monitor with DVI, and CPU with Dual or Single Link DVI capabilities

Package Includes

- DVI Dual Link TMDS cable - DVI-D, M/M, 25-ft. (7.62 m)



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.62
Cable Length (in.)	300
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	1.43
Shipping Weight (kg)	0.65
Unit Dimensions (hwd / in.)	12.000 x 10.000 x 0.500
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.