

## HDMI to DisplayPort Active Adapter Cable (M/M) - 4K, USB Power, Black, 2 m (6.6 ft.)

MODEL NUMBER: P567-02M



Connects a DisplayPort monitor or projector to the HDMI port on your Blu-ray player, computer, media server or other A/V source.

### Features

#### Active Adapter Cable Connects a 4K Monitor to Your Computer or Media Server

This all-in-one video converter cable lets you transmit 4K video with digital audio from the HDMI port on your Blu-ray player, satellite/cable box, computer or media server to your 4K DisplayPort-enabled monitor, projector or television. It's recommended for home theater systems, digital signage, trade show displays and conference room presentations. You can continue using your existing DisplayPort monitor without the expense of a new HDMI display to match your source device.

#### Transmits Crystal-Clear True 4K Video with Audio and 4:4:4 Color

The P567-02M supports Ultra HD video resolutions up to 4096 x 2160 (4K x 2K) at 30 Hz with rich, full 7.1-channel surround sound, 36-bit Deep Color, HDCP 1.4 and 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. Additionally, this cable transmits EDID information to ensure optimal display compatibility.

#### Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play cable requires no drivers or external power. The bus-powered cable receives any necessary extra power from the source device via the included USB-A connector. It is compatible with all HDMI sources and all major operating systems, including Windows, macOS and Linux. It is backward compatible with 1080p displays, so you can use the cable with older equipment.

## Specifications

OVERVIEW	
UPC Code	037332261274
Product Type	Active Cable
Technology	HDMI; DisplayPort
Cable Type	Active

### Highlights

- Supports UHD resolutions up to true 4K @ 30 Hz (4:4:4) for crystal-clear video
- Ideal for lectures, presentations, trade shows, digital signage and home theaters
- Bus-powered through USB connection to source; USB-A connector included
- Works with all HDMI sources and all major operating systems, including Windows
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Stream 4K movies and other programming from a Blu-ray player, game system or cable box to an HDTV
- Add a second monitor to your PC for multitasking purposes or editing video
- Upgrade the video quality of your digital signage to true 4K

### System Requirements

- Source device with HDMI output (Blu-ray player, computer, media server, etc.)
- Display device with DisplayPort input (monitor, television, projector, etc.)

### Package Includes

- P567-02M HDMI to DisplayPort 1.2 Active Adapter Cable, Black, 2 m (6.6 ft.)
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

VIDEO	
Max Supported Video Resolution	4096 x 2160 (4K) @ 30Hz
Max Supported Color Depth	36-bit Deep Color
HDR Support	No
Chroma Sub Sampling	4:4:4
AUDIO	
Audio Specification	7.1 Channel Surround Sound
INPUT	
Bus Powered	Yes
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	DISPLAYPORT (MALE); USB A (MALE)
Connector Plating	Gold
Contact Plating	Gold
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	6.0mm
Wire Gauge (AWG)	30
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Cable Length (in.)	79.2
Shipping Dimensions (hwd / in.)	0.91 x 6.50 x 5.32
Shipping Weight (kg)	0.10
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	USB-A: 5V/0.5A (2.5W)



Powering Business Worldwide

TRIPP LITE  
SERIES

COMMUNICATIONS	
EDID Compatible	Yes
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	Yes
IP68 Rated	No
IP20 Rated	No
Fully Molded Connector Ends	No
Displayport Specification	1.2
HDCP Specification	1.4
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.