

# AB Parallel Printer Cable (DB25 to Cen36 M/M), 6 ft. (1.83 m)

MODEL NUMBER: P606-006



## Highlights

- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing.

## System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed Bi-Directional communication (although not essential).

## Package Includes

- 6-ft. AB Parallel Printer Cable DB25M to Cen36M

## Features

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Length: 6-ft. Connectors: DB25 male/Cent36 male
- Nickel plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold

## Specifications

| OVERVIEW             |                      |
|----------------------|----------------------|
| UPC Code             | 037332013521         |
| Technology           | Parallel             |
| CONNECTIONS          |                      |
| Side A - Connector 1 | DB25 (MALE)          |
| Side B - Connector 1 | CENTRONICS 36 (MALE) |
| PHYSICAL             |                      |
| Color                | Black                |

|                                     |                           |
|-------------------------------------|---------------------------|
| Cable Jacket Color                  | Black                     |
| Cable Length (ft.)                  | 6                         |
| Cable Length (m)                    | 1.83                      |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50        |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27      |
| Shipping Weight (lbs.)              | 0.48                      |
| Shipping Weight (kg)                | 0.22                      |
| Unit Dimensions (hwd / in.)         | 0.000 x 0.000 x 0.000     |
| STANDARDS & COMPLIANCE              |                           |
| Product Compliance                  | RoHS                      |
| WARRANTY & SUPPORT                  |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.