


DisplayPort KVM Cable Kit - DP, USB, 3.5 mm Audio (3xM/3xM) + USB (M/M), 4K, 4:4:4, 10 ft. (3.05 m), Black

MODEL NUMBER: P783-010-U



DisplayPort KVM cable kit with DisplayPort, USB A/B and 3.5 mm plugs connects your computer to a Tripp Lite NIAP KVM Switch.

Features

10-ft. (3.05 m) Cables Connect Your DisplayPort Computer to a NIAP KVM Switch with CAC This DisplayPort cable kit includes two 10-ft. (3.05 m) cables for connecting a computer to a KVM switch with a Common Access Card (CAC) port. The P783-010 features DisplayPort, USB A/B and 3.5 mm audio connectors on both ends for connecting your computer to a KVM switch. The U022-010 is a USB cable that connects to the KVM's CAC port for accessing smart cards, scanners and biometric readers, including fingerprint readers, to bolster security.

Specifically Designed for Select KVMs to Save You Time and Money Recommended for the B002-HD1AC4 or other compatible NIAP KVM. The DisplayPort cable supports video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with true 4:4:4 chroma subsampling. The USB cables also support USB 2.0 data transfer speeds up to 480 Mbps. By combining several different cables into one convenient kit, you cut down on unnecessary clutter and costs.

Highlights

- Cuts cable clutter and saves money by combining essential KVM cables into just 2
- 10-ft. (3.05 m) 3-in-1 DP, USB A/B and 3.5 mm audio cable connects KVM to your computer
- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports true 4:4:4 chroma subsampling to meet latest color standards
- 10-ft. (3.05 m) USB A/B cable included for KVM's CAC port (smart cards, scanners, etc.)

Applications

- Connect a headless computer to a Tripp Lite KVM switch with CAC support
- Upgrade or replace worn or lost KVM cables
- Eliminate clutter and save money by replacing multiple cables with one new kit
- Extend the distance between the KVM switch and computer to 10 ft.

System Requirements

- B002-HD1AC4 NIAP KVM or other compatible KVM switch

Package Includes

- P783-010 DisplayPort KVM cable kit, 3 in 1 (M/M), 10 ft.
- U022-010 USB A/B cable (M/M), 10 ft.

Specifications

OVERVIEW	
UPC Code	037332241665
Accessory Type	Cable Kit
Technology	DisplayPort
Accessory Class	KVM Switch Accessories
VIDEO	
Max Supported Video Resolution	3840 x 2160 @ 60Hz



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB A (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	3.5MM (MALE); DISPLAYPORT (MALE); USB B (MALE)
Side B - Connector 2	USB B (MALE)
Contact Plating	Gold
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	1.10 x 8.10 x 10.50
Shipping Dimensions (hwd / cm)	2.79 x 20.57 x 26.67
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Relative Humidity	0-90% non-condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Displayport Specification	1.2
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.