

## 3.7kW Single-Phase Local Metered PDU, 208/230V (8 C13 & 2 C19), C20 / L6-20P Adapter, 12 ft. (3.66 m) Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20HV



### Highlights

- Local metered single phase 16A 208/230V PDU
- 1U horizontal rackmount; Digital current meter
- C20 input with L6-20P plug adapter; 12-ft. (3.66 m) line cord
- 10 total outlets (8 C13, 2 C19)
- Reversible housing; 6.5 in. / 16.5 cm depth
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

### Package Includes

- Rackmount PDU
- C19 to L6-20P plug adapter
- Rack mounting brackets

### Features

- 16/20A single phase 208/230V Local Metered Power Distribution Unit / rack PDU (rPDU) (Agency derated to 16A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- C20 inlet with C20 input cable and L6-20P adapter; 12-ft. (3.66 m) line cord
- 1U horizontal rackmount format installs in one rack space
- 10 total outlets (8 C13 / 2 C19)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks  
Back panel grounding lug
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

## Specifications

| OVERVIEW                       |                                      |
|--------------------------------|--------------------------------------|
| UPC Code                       | 037332159014                         |
| PDU Type                       | Local Metered                        |
| INPUT                          |                                      |
| Input Phase                    | Single-Phase                         |
| PDU Input Voltage              | 208; 230                             |
| Recommended Electrical Service | Single-phase 16/20A 230/208V service |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                              |                                                                                                            |
|----------------------------------------------|------------------------------------------------------------------------------------------------------------|
| Maximum Input Amps                           | 16                                                                                                         |
| Maximum Input Amps Details                   | Agency de-rated to 16A continuous                                                                          |
| Input Connection Type                        | C20 inlet                                                                                                  |
| PDU Plug Type                                | NEMA L6-20P; IEC-320 C20                                                                                   |
| Input Cord Details                           | Includes 12 ft. / 3.6m C19 to C20 power cable and L6-20P plug adapter                                      |
| Input Cord Length (ft.)                      | 12                                                                                                         |
| Input Cord Length (m)                        | 3.66                                                                                                       |
| <b>OUTPUT</b>                                |                                                                                                            |
| Output Capacity Details                      | 3.68kW (230V), 3.33kW (208V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet |
| Frequency Compatibility                      | 50 / 60 Hz                                                                                                 |
| Output Receptacle Details                    | Compatible with Eaton Tripp Lite Power Cords                                                               |
| Output Receptacles                           | (8) C13; (2) C19                                                                                           |
| Output Nominal Voltage                       | 208/230V                                                                                                   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |                                                                                                            |
| Front Panel LCD Display                      | Digital display reports total PDU output current in amps                                                   |
| <b>SURGE / NOISE SUPPRESSION</b>             |                                                                                                            |
| Automatic Shut-Off                           | No                                                                                                         |
| <b>PHYSICAL</b>                              |                                                                                                            |
| Material of Construction                     | Metal                                                                                                      |
| Rack Height                                  | 1U                                                                                                         |
| Form Factors Supported                       | 1U rackmount. Includes mounting accessories for 2-4 post racks                                             |
| Minimum Required Rack Depth (cm)             | 24.13                                                                                                      |
| Minimum Required Rack Depth (inches)         | 9.5                                                                                                        |
| PDU Form Factor                              | Horizontal (1U)                                                                                            |
| Shipping Dimensions (hwd / in.)              | 2.20 x 11.60 x 20.40                                                                                       |
| Shipping Dimensions (hwd / cm)               | 5.59 x 29.46 x 51.82                                                                                       |
| Shipping Weight (lbs.)                       | 7.50                                                                                                       |
| Shipping Weight (kg)                         | 3.40                                                                                                       |
| Unit Dimensions (hwd / in.)                  | 1.750 x 17.500 x 6.500                                                                                     |
| Unit Dimensions (hwd / cm)                   | 2,87 x 44,4 x 16,5                                                                                         |
| Unit Weight (lbs.)                           | 6.80                                                                                                       |
| Unit Weight (kg)                             | 3.08                                                                                                       |



Powering Business Worldwide

TRIPP LITE  
SERIES

| ENVIRONMENTAL                       |                                                                                                                   |
|-------------------------------------|-------------------------------------------------------------------------------------------------------------------|
| Operating Temperature Range         | 32° to 104°F (0° to 40°C)                                                                                         |
| Storage Temperature Range           | -22° to 122°F (-30° to 50°C)                                                                                      |
| Relative Humidity                   | 5% to 95% non-condensing                                                                                          |
| Operating Elevation                 | 0-10000 ft. (0-3000 m)                                                                                            |
| FEATURES & SPECIFICATIONS           |                                                                                                                   |
| Grounding                           | Rear grounding lug                                                                                                |
| STANDARDS & COMPLIANCE              |                                                                                                                   |
| Product Certifications              | IEC 62368-1; RETIE (Colombia); GOST (Russia); NOM (Mexico)                                                        |
| Product Compliance                  | RoHS; CE (Europe); EAC (Belarus, Kazakhstan, Russia); FCC Part 15 Class A (USA); UKCA; Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                  |                                                                                                                   |
| Product Warranty Period (Worldwide) | 2-year limited warranty                                                                                           |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.