

Power It! 2-Outlet In-Desk Power and Charging Dock - 4x USB-A, USB-B, HDMI, RJ11, RJ45, 10 ft. Cord, Antimicrobial Protection, Black

MODEL NUMBER: PS222DATAM



Installs level with your desktop surface to charge and power multiple devices simultaneously.

Features

Fits into Your Desktop Surface for Reliable Power and Charging

This Power It!® dock is designed for installation in your workspace's level surface, where its ports are within a convenient arm's reach. When not being used to power or charge devices or connect to a telephone or Ethernet network, you can close the flip-top cover flush against the tabletop to save valuable space. To connect devices, simply pop up the secure cover. This In-Desk Power and Charging Dock is ideal for home and office workstations with limited desk space.

A Variety of Ports and Outlets Accept a Wide Range of Electronic Devices

Two NEMA 5-15R outlets and two USB-A ports (4.5A combined) are available for powering and charging your laptop, tablet, smartphone or other devices. The PS222DATAM also features two USB-A data ports for transferring images, documents and other files, as well as ports for connecting HDMI, USB-B, telephone and Ethernet devices. The 10-foot (3-meter) input cord connects to a compatible AC wall outlet.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The PS222DATAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Highlights

- Installs flush with your tabletop surface to save space and offer easy access
- 2 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 2 USB-A ports share 4.5A for fast charging of phones and other mobile devices
- HDMI, USB-B, RJ11, RJ45 and 2 USB-A data ports connect a wide range of devices
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- PS222DATAM 2-Outlet In-Desk Power and Charging Dock
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332271891
Device Compatibility	Amazon Kindle; Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V



Powering Business Worldwide

TRIPP LITE
SERIES

Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	No
Right-Angle Outlets	No
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side A - Connector 2	(2) USB B (FEMALE)
Side A - Connector 3	HDMI (FEMALE)
Side A - Connector 4	RJ11 (FEMALE)
Side A - Connector 5	RJ45 (FEMALE)
Side B - Connector 1	(2) NEMA 5-15R
Side B - Connector 2	(4) USB A (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
Side B - Connector 4	RJ11 (FEMALE)
Side B - Connector 5	RJ45 (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	2
Total Charging Amps	4.5A
Total Charging Watts	22.5
Charging Method	USB



Powering Business Worldwide

TRIPP LITE
SERIES

Charging Port Type	(2) USB A (FEMALE)
Charging Ports / Amps	(1) 2.1A; (1) 2.4A
Charging Amps per Port	2.4A; 2.1A
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Plastic
Power Cord Color	Black
Mounting Location	Desktop
Housing Color	Black
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	9.06 x 6.30 x 4.72
Shipping Weight (kg)	1.05
Unit Dimensions (hwd / in.)	8.760 x 5.930 x 3.670
Unit Dimensions (hwd / cm)	8.76 x 5.93 x 3.67
Unit Weight (lbs.)	2.09
Unit Weight (kg)	0.95
Input Cord Color	Black
Mounting Details	Cut 7.95" (201.93 mm) x 4.06" (103.13 mm) hole for installation
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	No
Network Speed Support	1 Gbps (Gigabit)
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 308 (Canada); ICES (Canada); NOM (Mexico); UL 962A; UL Listed; cUL Listed
Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.