

8-Outlet Vertical Power Strip, 120V, 15A, NEMA 5-15P, 15 ft. (4.57 m) Cord, 24 in., Black Housing

MODEL NUMBER: **PS2408B**



Connect up to 8 electrical devices to a single AC wall socket. Ideal for connecting appliances, power tools, lighting and other electrical equipment in your home, office or work site.

Description

The PS2408B 8-Outlet Vertical Power Strip is a reliable 120V 1800W power strip that lets you connect up to eight electrical devices to a single AC wall socket. With a NEMA 5-15P plug and 15-ft. (4.57 m) AC power cord that reaches distant outlets and provides flexibility in placing the unit, this power strip is ideal for use with appliances, power tools, lighting and other electrical equipment in homes, offices and work sites.

Your components plug into eight NEMA 5-15R outlets designed to accommodate most AC adapters and transformers. Outlets are spaced 2.48 inches apart from center to center. Resettable 15A circuit breaker protects all outlets against dangerous overloads. Lighted on/off switch provides one-touch control over connected equipment. Switch's clear plastic cover prevents accidental shutdown.

Use the included hardware to mount the PS2408B in a horizontal or vertical position above your workbench, beneath your retail display, behind your desk or near your 19-inch rack enclosure. Its heavy-duty all-metal 24-inch black housing stands up to demanding network, laboratory or factory environments.

Features

Accepts Wide Range of Electronic Devices

- 8 NEMA 5-15R AC outlets accept most appliances, power tools, lights and other devices
- Spaced 2.48 in. apart to accommodate most AC adapters and transformers

Premium Safety Features

- Lighted on/off switch provides one-touch control over connected equipment
- Clear plastic switch cover prevents accidental shutdown
- Resettable 15A circuit breaker protects outlets against overloads

Fits Effortlessly Into Your Home, Office or Work Site

- 15-ft. (4.57 m) AC power cord with NEMA 5-15P plug long enough to reach distant outlets
- Designed for vertical or horizontal mounting using included hardware
- Black all-metal 24 in. housing stands up to rugged network, lab or factory environments

Highlights

- 8 NEMA 5-15R outlets accommodate most AC adapters
- 15A resettable circuit breaker
- 15-ft. (4.57 m) AC power cord with NEMA 5-15P plug
- Lighted on/off switch with clear plastic cover
- 24 in. housing designed for vertical or horizontal mounting

Package Includes

- PS2408B 8-Outlet Vertical Power Strip, Black Housing
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Specifications

OVERVIEW	
UPC Code	037332199829
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Right-Angle Outlets	No
Outlet Spacing	2.48 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Black
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	2.48 in.



Powering Business Worldwide

TRIPP LITE
SERIES

Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.40 x 28.00
Shipping Dimensions (hwd / cm)	6.10 x 11.18 x 71.12
Shipping Weight (lbs.)	3.10
Shipping Weight (kg)	1.41
Unit Dimensions (hwd / in.)	1.250 x 1.500 x 24.160
Unit Dimensions (hwd / cm)	3.175 x 61.37 x 3.81
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.45
Outlet Spacing	2.48 in.
Mounting Details	Includes mounting clips
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.