

Important Note

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 4x 15A Hospital-Grade Outlets, Safety Covers, 7 ft. Cord

MODEL NUMBER: PS-407-HG-OEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted 120V, 50/60 Hz power strip complies with UL 1363A specifications

Exclusive Antimicrobial Protection Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power 7-ft. (2.13 m) power cord with NEMA 5-15P-HG hospital-grade plug provides ample reach to the power source Rugged, all-metal housing for long life in demanding environments

Premium Safety Features Included locking outlet safety covers block access to unused outlets Dual resettable built-in 15A circuit breakers protect against dangerous overloads Switchless design prevents accidental shutoff

Ready to Use Right Out of the Box Built-in mounting tabs and flanges for easy installation on a variety of surfaces

Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A and NFPA 99 specifications
- 4 NEMA 5-15R-HG outlets with locking safety covers
- 7 ft. (2.1 m) cord with NEMA 5-15P-HG plug reaches nearby outlets

Package Includes

- PS-407-HG-OEM UL 1363A Medical-Grade Power Strip, 7-ft. (2.13 m) cord
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332203632
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	7
Right-Angle Plug	No
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Mounting Holes or Slots	Yes
Outlets Measurement (Center to Center)	Inner outlets = 1.27 in.



Powering Business Worldwide

TRIPP LITE
SERIES

Receptacle Color	White
Shipping Dimensions (hwd / in.)	9.88 x 6.22 x 2.44
Shipping Dimensions (hwd / cm)	25.10 x 15.80 x 6.20
Shipping Weight (lbs.)	2.36
Shipping Weight (kg)	1.07
Unit Dimensions (hwd / in.)	1.730 x 2.500 x 8.540
Unit Dimensions (hwd / cm)	21.97 x 6.35 x 3.81
Unit Weight (lbs.)	2.77
Unit Weight (kg)	1.26
Mounting Details	Includes flanges
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1363A
Product Compliance	NFPA 99: 10.2.3.6; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.