

# 1U Rack-Mount Power Strip, 120V, 15A, 5-15P, 12 Outlets (6 Front-Facing, 6-Rear-Facing), 15 ft. (4.57 m) Cord

MODEL NUMBER: RS-1215



## Highlights

- Designed for standard 19-inch racks (1U high)
- 12 outlets (6 front / 6 rear)
- 15-amp circuit breaker
- 15-ft. (4.57 m) cord

## Package Includes

- RS-1215
- Mounting hardware
- Instruction manual

## Description

The RS-1215 Power Strip offers 15A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rack-mount, wall-mount and under-counter installation. Uses only 1U when installed in any 19-inch rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215 ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA 5-15R outlets (six front/six rear), 15-foot (4.6-meter) cord and lighted switch with cover prevents risk of accidental turn-off.

## Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 NEMA5-15R output receptacles (6 front/6 rear)
- 15-ft. (4.57 m) AC cord NEMA5-15P plug connection
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332011534 |
| INPUT    |              |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                              |                                                                                    |
|----------------------------------------------|------------------------------------------------------------------------------------|
| Nominal Input Voltage(s) Supported           | 120V AC                                                                            |
| Recommended Electrical Service               | 15A 120V                                                                           |
| Voltage Compatibility (VAC)                  | 120                                                                                |
| Input Plug Type                              | NEMA 5-15P                                                                         |
| Input Cord Length (ft.)                      | 15                                                                                 |
| Right-Angle Plug                             | No                                                                                 |
| Input Cord Length (m)                        | 4.57                                                                               |
| Integrated Cord Clip                         | No                                                                                 |
| <b>OUTPUT</b>                                |                                                                                    |
| Frequency Compatibility                      | 50 / 60 Hz                                                                         |
| Output (Watts)                               | 1800                                                                               |
| Output Receptacles                           | (12) 5-15R                                                                         |
| Circuit Breaker (amps)                       | 15                                                                                 |
| Transformer Accommodation                    | (5) Yes                                                                            |
| Outlet Orientation                           | 6 front facing / 6 rear facing                                                     |
| Right-Angle Outlets                          | No                                                                                 |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |                                                                                    |
| Switches                                     | Lighted 2 position switch controls power to all outlets                            |
| Locking Switch Cover                         | Transparent locking switch cover prevents accidental shutoff                       |
| <b>PHYSICAL</b>                              |                                                                                    |
| Color                                        | Black                                                                              |
| Material of Construction                     | Metal                                                                              |
| Power Cord Color                             | Black                                                                              |
| Form Factors Supported                       | 1U rackmount, wall-mount and undercounter installation supported                   |
| Mounting Holes or Slots                      | No                                                                                 |
| Outlets Measurement (Center to Center)       | Distance between Front outlets = 3.28 in.; Distance between Rear outlets = 4.5 in. |
| Receptacle Color                             | Black                                                                              |
| Shipping Dimensions (hwd / in.)              | 2.00 x 9.30 x 20.50                                                                |
| Shipping Dimensions (hwd / cm)               | 5.08 x 23.62 x 52.07                                                               |
| Shipping Weight (lbs.)                       | 5.57                                                                               |
| Shipping Weight (kg)                         | 2.53                                                                               |
| Unit Dimensions (hwd / in.)                  | 1.750 x 17.500 x 4.000                                                             |
| Unit Dimensions (hwd / cm)                   | 4.445 x 44.45 x 11.4                                                               |
| Unit Weight (lbs.)                           | 4.6                                                                                |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                       |
|-------------------------------------|---------------------------------------|
| Unit Weight (kg)                    | 2.09                                  |
| Mounting Details                    | Includes Rackmount flanges            |
| FEATURES & SPECIFICATIONS           |                                       |
| Antimicrobial                       | No                                    |
| Built-In Circuit Breaker            | Yes                                   |
| Grounding                           | Back panel nut and bolt grounding lug |
| STANDARDS & COMPLIANCE              |                                       |
| Product Certifications              | cUL Listed; UL 1363; UL Listed        |
| Product Compliance                  | RoHS                                  |
| WARRANTY & SUPPORT                  |                                       |
| Product Warranty Period (Worldwide) | Lifetime limited warranty             |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.