



Powering Business Worldwide

TRIPP LITE
SERIES

6-Outlet Surge Protector, Direct Plug-In, 750 Joules, Diagnostic LED, Black

MODEL NUMBER: SK6-0B



Highlights

- 6 outlets/direct plug-in
- 750 joule rating

Package Includes

- SK6-0B Surge Suppressor
- Warranty information
- Instruction manual

Description

The SK6-0B Surge Suppressor is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features 6 outlets and 750 joules of surge energy absorption. \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 6 outlets: direct plug-in
- Surge energy absorption: 750 joules
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332146397
Charging Form Factor	Direct Plug-In
Product Type	Surge Protector
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green - Protected; Red - Grounded
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 500, 500
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No



Powering Business Worldwide

TRIPP LITE
SERIES

Outlets Measurement (Center to Center)	Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	6.30 x 8.70 x 1.50
Shipping Dimensions (hwd / cm)	16.00 x 22.10 x 3.81
Shipping Weight (lbs.)	0.61
Shipping Weight (kg)	0.28
Unit Dimensions (hwd / in.)	3.700 x 5.000 x 1.200
Unit Dimensions (hwd / cm)	1.45 x 1.97 x .47
Unit Weight (lbs.)	2.65
Unit Weight (kg)	1.20
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.