

Protect It! 6-Outlet Surge Protector - 5-15R Outlets, USB-C and USB-A Ports, 5-15P Direct Plug-In, 1080 Joules, Gray

MODEL NUMBER: SK60C



Protects your computer and other home/office electronics against dangerous power surges, spikes and line noise.

Features

6-Outlet Surge Protector with USB Charging Safeguards Your Sensitive Electronics

Ideal for your home, office, retail or industrial workstation, this Protect It!® surge protector features a surge protection rating of 1080 joules to defend your valuable electronic components against power surges and spikes. The unit plugs directly into a wall outlet, avoiding annoying cord clutter.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp and other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

USB Charger Keeps Mobile Devices Ready for Use

One USB-C port and two USB-A ports are available for charging your smartphone, tablet or other USB mobile devices. The USB-C port has 3A and the USB-A ports 2.4A each for charging multiple devices at the same time. A green LED confirms at a glance that your equipment is protected.

Highlights

- 6 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 1080 joules protect your valuable electronics against dangerous surges and spikes
- Plugs directly into the wall (no cord required) for easy installation and no cable clutter
- USB-A and USB-C ports power and charge smartphones and other mobile devices
- Easy-to-see green LED lets you know at a glance that your equipment is protected

Package Includes

- SK60C 6-Outlet Surge Protector, Gray
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332288783
Product Type	Surge Protector
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Capacity (Watts)	1875
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	No
Output Amp Capacity	15
Right-Angle Outlets	No
CONNECTIONS	
Number of Ports	3
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green - Protected
CHARGING	
Number of Charging Ports	3
Total Charging Amps	2.4A each for 2 USB-A and 3A for USB-C
Total Charging Watts	1875
Charging Method	USB
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports / Amps	(2) 2.4A; (1) 3A
Overcharge Protection	No
Charging Amps per Port	2.A each for USB-A and 3A for USB-C



Powering Business Worldwide

TRIPP LITE
SERIES

SURGE / NOISE SUPPRESSION

AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	L-N, L-G, N-G
UL1449 Let Through Rating	500, 500, 600
EMI / RFI Filtering	150KHz-100MHz
Isolated Filter Banks	no
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes

DATALINE SURGE SUPPRESSION

Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No

PHYSICAL

Color	Gray
Material of Construction	Plastic
Housing Color	Gray
Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	5.76 x 4.16 x 2.60
Shipping Dimensions (hwd / cm)	14.63 x 10.57 x 6.60
Shipping Weight (lbs.)	0.66
Shipping Weight (kg)	0.30
Unit Dimensions (hwd / in.)	5.520 x 3.920 x 2.270
Unit Dimensions (hwd / cm)	14.2 x 9.1 x 7.1
Unit Weight (lbs.)	0.57
Unit Weight (kg)	0.26

ENVIRONMENTAL

Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH

FEATURES & SPECIFICATIONS



Powering Business Worldwide

TRIPP LITE
SERIES

Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 286 (Canada); CAN/CSA-C22.2 No. 42 (Canada); UL 1449
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$7,500 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.