

SmartPro 1440VA 1440W 120V Line-Interactive Sine Wave UPS - 8 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower, TAA

MODEL NUMBER: SMART1500RXLTA



Provides complete battery backup and pure sine wave power output for servers, switches and other high-end distributed IT equipment.

Features

1.44kVA/1.44kW/120V Battery Backup for Distributed IT, Telecom or Enterprise Deployments

This line-interactive UPS system provides reliable battery backup and AC power protection against blackouts, brownouts, surges and line noise that can damage your valuable IT equipment. The SMART1500RXLTA is ideal for large and small network devices, high-end workstations, storage and security equipment in labs, server rooms and data centers.

Reliable, Expandable Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable VRLA battery modules allow you to work through short power failures and give you enough time to safely save files and shut down your system in case of a prolonged blackout. Switchover from line to battery power happens within milliseconds to maintain continuous operation of connected equipment without interruption or rebooting. Extra runtime is available by connecting up to four optional extended battery modules (BP48VRXLTA, sold separately). The SMART1500RXLTA restarts automatically once power is restored, regardless of battery charge level, saving you a costly site visit.

Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

Built-in AVR corrects abnormal voltage conditions without using the battery. The SMART1500RXLTA maintains regulated 120V nominal output during brownouts and overvoltages from 80V to 151V while keeping the battery fully charged and ready to take over in case of power failure.

Pure Sine Wave Output and Unity Power Factor

Pure sine wave output power ensures maximum stability while unity power factor ensures the most watts possible at each power rating, providing maximum compatibility with sensitive equipment.

Optional LXE Network Management Card Allows Remote Control and Access 24/7

The WEBCARDLXE (sold separately) enables access to advanced features like switchable load banks, automatic email messaging on power events, and full remote control of the UPS. The IP-based Auto Probe feature ensures network uptime by communicating with other network devices and automatically rebooting IT equipment when a loss of connectivity is detected. **Note:** The SMART1500RXLTA is not compatible with WEBCARDLX.

Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Pure sine wave output ensures maximum stability and compatibility with equipment
- Automatic voltage regulation corrects abnormal voltage conditions without using the battery
- Add external battery modules (sold separately) to extend UPS runtime during power outages
- WEBCARDLXE (sold separately) allows full remote control of UPS and access to advanced features

Package Includes

- 1440VA 1440W 120V Line-Interactive UPS
- USB cable
- DB9 cable
- Rack-mounting hardware
- Tower support stands
- Safety instructions
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

NEMA 5-15R Outlets Protect Your Connected Components

Eight managed 5-15R outlets provide connected equipment with pure sine wave AC output and allow you to monitor power consumption down to the outlet group level. Power provided by these outlets is filtered to protect connected equipment against damaging surges and line noise. Four outlets are grouped into two programmable load banks that let you shed non-critical loads to extend runtime for critical loads. Front and rear cooling fans help protect equipment from overheating.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

ENERGY STAR-Certified to Help You Save Money and Protect the Environment

By meeting strict U.S. Department of Energy and U.S. Environmental Protection Agency requirements, this ENERGY STAR 2.0 UPS system provides high operational efficiency to signal a reduction in BTU emissions, save on utility and cooling costs and help protect the environment.

Intuitive Front-Panel Interface for Convenient UPS Operation and Monitoring

The two-line front-panel LCD monitoring screen features 10 selectable screens that allow quick access to a wide range of detailed UPS and site power information. LEDs show UPS status: a green light means utility power is on, an orange light means the UPS is in battery mode and a red light indicates an active alarm or fault. The control panel rotates to accommodate both rack-mount and tower configurations.

Advanced Communications Ports Allow for Automatic Saves and Shutdowns

RS-232 and USB ports connect to a device for a variety of communication options (cables are included). A dry-contact relay port can be programmed through the LCD to provide reliable communications to automation and industrial components. The RPO/ROO port permits emergency shutdown or remote restart of all connected equipment.

Versatile Installation Options

You can mount the SMART1500RXLTA in just 2U of space in an EIA-standard 19-inch rack using the included hardware. You can also adapt it for tower installation using the included support stands. The 10-foot power cord with NEMA 5-15P plug connects to a compatible AC outlet.

TAA-Compliant for GSA Schedule Purchases

The SMART1500RXLTA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	786689816063
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	80V-151V (normal mode); adjustable to 70V-153V (extended mode)
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	10



Powering Business Worldwide

TRIPP LITE
SERIES

UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Maximum Input Amps	12
OUTPUT	
Output Capacity (VA)	1440
Output Capacity (kVA)	1.44
Output Capacity (Watts)	1440
Output Capacity (kW)	1.44
Power Factor	1
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Output Voltage Regulation (Line Mode)	120V (-13%, +15%)
Output Voltage Regulation (Battery Mode)	-10%, +6%
Load Management Receptacles	Two switchable two-outlet 5-15R load banks
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 120V; 125V
Output Receptacles	(8) 5-15R
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	5.1 min. (1440w)
Runtime Half Load (min.)	15.1 min. (720w)
Expandable Runtime	Yes
Expandable Battery Runtime	Extended runtime supported via optional Tripp Lite Series 48V DC BP48VRXLTAA ; external battery packs only.
Expandable Runtime Description	BP48VRXLTAA ; (Limit 4)
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90% (typical, full load discharge)
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	EBP-1614
Battery Replacement Description	Hot-swappable, user replaceable batteries



Powering Business Worldwide

TRIPP LITE
SERIES

VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 80V to 151V (Normal Mode) or 70V-153V (Extended Mode)
Overvoltage Correction	Reduces incoming voltage between 132V-151V (Normal Mode) or 138V-152V (Extended mode) by 13%
Undervoltage Correction	Boost incoming voltages between 81V-102V (Normal Mode) or 71V-92V (Extended Mode) by 15%
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Front panel rotatable LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, frequency, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	5 pushbutton switches control OFF / ON power status, ENTER, UP, and DOWN selection and ESC control functions
Alarm Cancel Operation	Press the ESC (Escape) button on the front panel display to silence the alarm. Check the alarm condition and perform the applicable action to resolve the condition. If the alarm status changes, the alarm beeps again, overriding the previous alarm silencing
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
LED Indicators	UPS status (Solid Green); Battery Mode (Solid Orange) / Battery Low Warning (Flashing Orange); Fault/Alarm (Solid Red)
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	380
AC Suppression Response Time	Instantaneous
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	2U
Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; Tower
Installation Form Factors Supported with Optional Accessories	4 post rackmount short-depth (4POSTRAILKITWM)
Maximum Device Depth (cm)	44.70
Maximum Device Depth (in.)	17.6
Maximum Device Depth (mm)	447
Minimum Required Rack Depth (cm)	53.34
Minimum Required Rack Depth (inches)	21
Minimum Required Rack Depth with External Battery Pack (cm)	51
Minimum Required Rack Depth with External Battery Pack (in.)	20
Minimum Required Rack Depth without External Battery Pack (cm)	53



Powering Business Worldwide

TRIPP LITE
SERIES

Minimum Required Rack Depth without External Battery Pack (in.)	21
Optional Mounting Accessory Notes	 4POSTRAILKITWM enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm)
Primary UPS Depth (mm)	447
Primary UPS Height (mm)	86
Primary UPS Width (mm)	437
Shipping Dimensions (hwd / in.)	9.45 x 19.60 x 23.03
Shipping Weight (kg)	28.00
UPS Housing Material	Metal
UPS Power Module Dimensions (hwd, in.)	3.4 x 17.2 x 17.6
UPS Power Module Weight (kg)	23.00
UPS Power Module Weight (lbs.)	50.71
Unit Dimensions (hwd / in.)	3.450 x 17.200 x 17.600
Unit Weight (lbs.)	50.706
Unit Weight (kg)	23.00
Mounting Details	Included 4-post mounting kit enables installation in 4 post racks. Two ABS mounting stands enables the UPS to be configured in an upright tower orientation.
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	20 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	83
AC Mode Efficiency Rating (100% Load)	96%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	504
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	0-32,808
Audible Noise	45 dBA maximum, front side 1m
COMMUNICATIONS	
Network Management Cards	 WEBCARDLXE
Network Monitoring Port Description	Gain access to advanced features and complete remote control of the UPS via the WEBCARDLXE. Not compatible with WEBCARDLX.
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Office software at https://www.tripplite.eaton.com/poweralert
Communications Cable	USB and DB9 cabling included



Powering Business Worldwide

TRIPP LITE
SERIES

Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite
Network Management Card Description	One slot for optional WEBCARDLXE web card. Note: Not compatible with WEBCARDLX
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
Emergency Power Off (EPO)/Remote On-Off (ROO)	Yes
LINE / BATTERY TRANSFER	
Transfer Time	4 milliseconds (AC to battery mode), 1 millisecond (Battery to AC mode)
Low Voltage Transfer to Battery Power (Setpoint)	80 (70V in extended mode)
High Voltage Transfer to Battery Power (Setpoint)	151
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic Voltage Regulation (AVR); Expandable battery backup; Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
Grounding Details	Back panel grounding lug
APPLICATIONS	
UPS Applications	Large Network; High-End Desktop/Small Network
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); ICES (Canada); NOM (Mexico); UL 1778
Product Compliance	CE (Europe); ENERGY STAR Qualified; FCC Part 15 Class A (USA); RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.